



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street
88201-0000, NM Roswell
Phone: 575-208-1571
Fax: 575-208-1572



JJS25 Tron Fast Acting Fuse Class T

Bussmann Fuses

Catalog Number	JJS25
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series JJS Fuse, Current-Limiting, Small Footprint, VFD Line Protection, 25 A, Class T, Non-Indicating, Ferrule End X Ferrule End, 200 Kaic At 600 V, Standard, 10, 600 V
Weight per unit	0.1500 (lbs/each)
Product Category	Renewable & Non-Renewable

Features

amperage rating	25
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.5600 IN X 0.5600 IN
Fuse Class	Class T
interrupt rating	200 kAIC at 600 Vac
media	Yes
Voltage Rating	600 V

Dimensions and Weight

Size	0.56 In Diameter X 1.50 In Length
------	-----------------------------------

Descriptions

Description	TRON FAST ACTING FUSE CLASS T
extra long description	BUSS JJS-25 TRON FAST ACTING FUSE C
Features	Bussmann's Class T current-limiting, fast-acting fuses. Provides 10X better current limitation to help prevent equipment damage caused by short-circuit events. 200 kA Interrupting rating complies with NEC Section 110.9 for today's large capacity systems. Small, space-saving fuses provide a high degree of current limitation on short-circuits for excellent component protection.
Long Description	Eaton Bussmann series JJS fuse, Current-limiting, Small footprint, VFD line protection, 25 A, Class T, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 V, Standard, 10, 600 V
Product Type	Tron Fast Acting Fuse Class T
Special Features	Small Footprint

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712628259
Manufacturers Part Number	JJS-25
UPC	051712628259



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street
88201-0000, NM Roswell
Phone: 575-208-1571
Fax: 575-208-1572

Taxonomies, Classifications, and Categories

Category Description Fuses & Fuse Accessories

Type FUSE

Packaging

Carton 1

Package 10

Weight Per each 0.15

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Safety and Security Systems

standard CE Marked, RoHS Compliant