

# Specifications



## Eaton JM60100-3CR

Eaton Bussmann series JM modular fuse block, CR, 70-100 A, Three-pole, Class J, Knife blade end x knife blade end, 200 kAIC, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series JM modular fuse block
<b>CATALOG NUMBER</b>	JM60100-3CR
<b>UPC</b>	051712391269
<b>PRODUCT LENGTH/DEPTH</b>	5.4 in
<b>PRODUCT HEIGHT</b>	2.95 in
<b>PRODUCT WIDTH</b>	5.93 in
<b>PRODUCT WEIGHT</b>	0.95 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Listed CSA Certified



Powering Business Worldwide

## Electrical rating

<b>AMPERAGE RATING</b>	70-100A
<b>INTERRUPT RATING</b>	200 kAIC
<b>SHORT-CIRCUIT RATING</b>	200 kA
<b>VOLTAGE RATING</b>	600 V

## General information

<b>CLASS</b>	Class J
<b>CONNECTION</b>	Knife blade end x knife blade end
<b>SPECIAL FEATURES</b>	CR

## Physical details

<b>NUMBER OF POLES</b>	Three-pole
------------------------	------------

## Resources

CATALOGS	<a href="#">eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf</a> <a href="#">Bussmann series complete full line catalog no. 1007</a>
CERTIFICATION REPORTS	<a href="#">Eaton Bussmann EU Declaration of conformity 93-68-EEC2201</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - JM60100-3CR</a>
TECHNICAL DATA SHEETS	<a href="#">JM60100-3CR~100 amp class J fuse holder 600V -3 pole</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Datasheet - FNQ-30</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton JM60100-3CR

Eaton Bussmann series JM modular fuse block, CR, 70-100 A, Three-pole, Class J, Knife blade end x knife blade end, 200 kAIC, 600 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series JM modular fuse block
<b>CATALOG NUMBER</b>	JM60100-3CR
<b>UPC</b>	051712391269
<b>PRODUCT LENGTH/DEPTH</b>	5.4 in
<b>PRODUCT HEIGHT</b>	2.95 in
<b>PRODUCT WIDTH</b>	5.93 in
<b>PRODUCT WEIGHT</b>	0.95 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	Contact Manufacturer UL Listed CSA Certified



Powering Business Worldwide

## Electrical rating

AMPERAGE RATING	70-100A
INTERRUPT RATING	200 kAIC
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	600 V

## General information

CLASS	Class J
CONNECTION	Knife blade end x knife blade end
SPECIAL FEATURES	CR

## Physical details

NUMBER OF POLES	Three-pole
-----------------	------------

## Resources

CATALOGS	<a href="#">eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf</a> <a href="#">Bussmann series complete full line catalog no. 1007</a>
CERTIFICATION REPORTS	<a href="#">Eaton Bussmann EU Declaration of conformity 93-68-EEC2201</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - JM60100-3CR</a>
TECHNICAL DATA SHEETS	<a href="#">JM60100-3CR~100 amp class J fuse holder 600V -3 pole</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Datasheet - FNQ-30</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.