

Specifications

Eaton JP60030-3CR



Eaton Bussmann series JP pyramid fuse block, CR, 30 A, Class J, 200 kAIC, Thermoplastic, Panel, 600 V, #14-2 AWG Cu/Al

General specifications

PRODUCT NAME	Eaton Bussmann series JP pyramid fuse block
CATALOG NUMBER	JP60030-3CR
UPC	051712434164
PRODUCT LENGTH/DEPTH	0.001 in
PRODUCT HEIGHT	0.001 in
PRODUCT WIDTH	0.001 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed CSA Certified

Electrical rating

AMPERAGE RATING	30 A
INTERRUPT RATING	200 kAIC
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	600 V

General information

CLASS	Class J
MOUNTING METHOD	Panel
SPECIAL FEATURES	CR

Physical details

MATERIAL	Thermoplastic
WIRE SIZE	#14-2 AWG Cu/Al

Resources

CATALOGS	eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf
	Bussmann series full line catalog 1007, section 8 fuse blocks and holders
	Bussmann series complete full line catalog no. 1007
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2201
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - JP60030-3CR
TECHNICAL DATA SHEETS	JP60030-3CR~J PYRAMID FUSE BLOCK
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton JP60030-3CR



Eaton Bussmann series JP pyramid fuse block, CR, 30 A, Class J, 200 kAIC, Thermoplastic, Panel, 600 V, #14-2 AWG Cu/Al

General specifications

PRODUCT NAME	Eaton Bussmann series JP pyramid fuse block
CATALOG NUMBER	JP60030-3CR
UPC	051712434164
PRODUCT LENGTH/DEPTH	0.001 in
PRODUCT HEIGHT	0.001 in
PRODUCT WIDTH	0.001 in
PRODUCT WEIGHT	0.7 lb
WARRANTY	Not Applicable
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed CSA Certified

Electrical rating

AMPERAGE RATING	30 A
INTERRUPT RATING	200 kAIC
SHORT-CIRCUIT RATING	200 kA
VOLTAGE RATING	600 V

General information

CLASS	Class J
MOUNTING METHOD	Panel
SPECIAL FEATURES	CR

Physical details

MATERIAL	Thermoplastic
WIRE SIZE	#14-2 AWG Cu/Al

Resources

CATALOGS	eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf
	Bussmann series full line catalog 1007, section 8 fuse blocks and holders
	Bussmann series complete full line catalog no. 1007
CERTIFICATION REPORTS	Eaton Bussmann EU Declaration of conformity 93-68-EEC2201
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - JP60030-3CR
TECHNICAL DATA SHEETS	JP60030-3CR~J PYRAMID FUSE BLOCK
TECHNICAL SERVICE BULLETINS	Datasheet - FNQ-30

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

