



KA29U, AL Set Screw Connector, 1-Hole, #6 AWG Str-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated

By Burndy
Catalog # [KA29U](#)



Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-250 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated.

Application

For Aluminum And Copper Conductors

General

Connector Type	Terminal
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	275 LBS/in
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Sub Brand	UNIVERSAL TERM
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810370155

Dimensions

Dimension - Bolt Hole Size inch	0.31 in
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.94 in
Dimension - Height fraction	1.14 in
Dimension - Height inch	1.14 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - N inch	0.47 in
Dimension - Pad Width inch	1.02 in
Dimension - Stud Size inch	5/16
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - AL Str Size	6;4;3;2;1;1/0;2/0;3/0;4/0;250
Conductor - AL Str Size Range	6-250
Conductor - Copper Str Size	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size Range	6-250
Conductor - Nominal Diameter	0.184, 0.184, 0.206, 0.232, 0.232, 0.260, 0.260, 0.292, 0.320, 0.328, 0.360, 0.368, 0.390, 0.414, 0.438, 0.464, 0.492, 0.522, 0.528, 0.574, 0.600
Conductor Size	6 AWG-250 KCMIL
Conductor Type	<ul style="list-style-type: none">AL C Str-SizeCU C Str-SizeCU C Solid-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	400
Minimum Pack Quantity	25

Product Assets

[3D Models - KA29U_MODEL-STEP](#)
[3D Models - KA29U_MODEL-PDF](#)
[3D Models - KA29U_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - se210997](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-KA29U-SPEC-EN | REV 8/2023