



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604



KTK2 2A 600V Fa Midget Fuse

Bussmann Fuses

Catalog Number	KTK2
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series KTK Fuse, Control Circuits, Lighting Circuit Protection, Meter Circuits, 2 A, Non-Indicating, Ferrule End X Ferrule End, 100 Kaic At 600 V, Melamine Tube, Nickel-Plated Bronze Endcap, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	2 AMP
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
interrupt rating	100000 Amp (RMS Symmetrical UL)
Material	Melamine Tube; Nickel-plated bronze endcap
Voltage Rating	600 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	2A 600V FA MIDGET FUSE
extra long description	BUSS KTK-2 LIMITRON FAST ACTING FUS
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series KTK fuse, Control circuits, Lighting circuit protection, Meter circuits, 2 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, Melamine tube, Nickel-plated bronze endcap, 600 V
Product Type	Limitron Fast Acting Fuse
Special Features	Nickel Plated Bronze Endcap

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712420129
Manufacturers Part Number	KTK-2
UPC	051712420129



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	10
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked