



# ESSENTIAL SERIES

## GENERAL PURPOSE LED BULBS

### KT-LED7.5R20-8XX

#### REPLACEMENT LAMP

#### DESCRIPTION

7.5W R20 Lamp | 2700–5000K | >80 CRI | Standard Flood



<b>LAMP TYPE:</b> R20
<b>BASE TYPE:</b> E26 (Medium)
<b>WATTAGE:</b> 7.5W
<b>COLOR TEMPERATURE:</b> 2700–5000K
<b>COLOR RENDERING INDEX (CRI):</b> >80
<b>WARRANTY:</b> 3 Years
<b>RATED LIFE:</b> L70 (15,000 Hours)



#### TYPICAL APPLICATIONS

- Recessed downlights
- Track lighting
- Surface-mount ceiling fixtures

#### PRODUCT FEATURES

- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, uniform dimming
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- Suitable for use in damp locations
- Operating temperature range –4°F/–20°C to 95°F/35°C
- PF >0.90
- ANSI compliant construction ensures fitment for intended applications
- UL Listed
- Meets Energy Star requirements
- Complies with Part 15 of FCC


#### ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED7.5R20-827	R20 bulb; Standard flood; Dimmable	2700K	120V	7.5W	50W halogen	E26	525 lm	>80	120°	Yes	70 lm/W
KT-LED7.5R20-830	R20 bulb; Standard flood; Dimmable	3000K	120V	7.5W	50W halogen	E26	525 lm	>80	120°	Yes	70 lm/W
KT-LED7.5R20-835	R20 bulb; Standard flood; Dimmable	3500K	120V	7.5W	50W halogen	E26	525 lm	>80	120°	Yes	70 lm/W
KT-LED7.5R20-840	R20 bulb; Standard flood; Dimmable	4000K	120V	7.5W	50W halogen	E26	525 lm	>80	120°	Yes	70 lm/W
KT-LED7.5R20-850	R20 bulb; Standard flood; Dimmable	5000K	120V	7.5W	50W halogen	E26	525 lm	>80	120°	Yes	70 lm/W

## KT-LED7.5R20-8XX

### REPLACEMENT LAMP

#### PHYSICAL CHARACTERISTICS



#### LAMP DIMENSIONS

A (Diameter)	2.48"
B (Length)	3.78"

BASE TYPE: E26 (Medium)

#### PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	16.02" × 13.46" × 9.06"
Carton Weight	12.9 lbs

#### ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	EASY CODE	UPC
KT-LED7.5R20-827	6 pcs	NHE-36	843654127439
KT-LED7.5R20-830	6 pcs	HEK-35	843654127446
KT-LED7.5R20-835	6 pcs	BAE-22	843654130316
KT-LED7.5R20-840	6 pcs	DXH-68	843654127453
KT-LED7.5R20-850	6 pcs	BYK-44	843654127460

#### CATALOG NUMBER BREAKDOWN

# KT-LED7.5R20-8XX

1 2 3 4 5 6

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 800 Series
- 6 Color Temperature