



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave
76301-0000, TX Wichita Falls
Phone: 940-257-6832
Fax: 940-257-6833

KTVTLED444A840VD 4' 44W Vaportite 40K 5720LM

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | KTVTLED444A840VD |
| Manufacturer | Keystone Technologies |
| Description | 44W Led Vapor Tight, 4FT Narrow Body, 120-277V Input, Frosted Lens, 4000K, 0-10V Dimmable, Premium Series |
| Weight per unit | 4.6 (lbs/each) |
| Product Category | Led Vapor Tight Lighting |

Features

| | |
|-----------------|-------------|
| Ballast Type | N/A |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 5720 |
| Nominal Length | N/A |
| Nominal Size | 4 ft Linear |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 44 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | N/A |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | Gray |

Descriptions

| | |
|------------------------|---|
| Construction | IP66 |
| Description | 4' 44W VAPORTITE 40K 5720LM |
| extra long description | Key KT-VTLED44-4A-840-VDIM-P 44W LE |
| Long Description | 44W LED VAPOR TIGHT, 4FT NARROW BODY, 120-277V INPUT, FROSTED LENS, 4000K, 0-10V DIMMABLE, PREMIUM SERIES |
| Product Type | 44W Led Vapor Tight, 4FT Narrow Body, 120-277V Input, Froste |

Manufacturer Information

| | |
|---------------------------|--------------------------|
| Brand | Keystone |
| GTIN | 00843654122175 |
| Manufacturers Part Number | KT-VTLED44-4A-840-VDIM-P |
| UPC | 843654122175 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave
76301-0000, TX Wichita Falls
Phone: 940-257-6832
Fax: 940-257-6833

Taxonomies, Classifications, and Categories

Category Description LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING

Packaging

Carton 1

Package 4

Weight Per each 4.6

Uses, Certifications, and Standards

Energy Star N