



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L111209C Ty-Raps

*Thomas&Betts-Abb Ins Prod*

Catalog Number	L111209C
Manufacturer	Thomas&Betts-Abb Ins Prod
Description	
Weight per unit	0.0100 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Bundle Diameter	0.187 Inches/4.76mm-3.0 Inches/76.2mm
Material	Nylon/Polyamide 6.6
Tensile Strength	120 Pounds/534 Newtons

### Material, Color, and Finish

Color	IVORY
-------	-------

### Dimensions and Weight

Length	11.77 Inches/299mm
Thickness	0.06 Inches/1.6mm
Width	0.30 Inches/7.6mm

### Descriptions

Description	TY-RAPS
Product Type	Cable Tie 120LB 11IN Natural Nylon

### Manufacturer Information

Brand	Catamount
GTIN	00728494111919
Manufacturers Part Number	L-11-120-9-C
UPC	728494111919

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Heavy-Duty Cable Tie

### Packaging


Carton	100
Package	4000
Weight Per each	0.01

### Uses, Certifications, and Standards

standard	UL E49405
----------	-----------



# Catamount®

**NOTES:**

1. MATERIAL: NYLON 6,6
2. FLAMMABILITY: UL94V-2
3. OPERATING TEMPERATURE RANGE: -40°F [-40°C] TO 185°F [85°C]
4. MINIMUM TENSILE RATING: 120 LBS [534 N]
5. MINIMUM WIRE BUNDLE: .188 [4,76]
6. MAXIMUM WIRE BUNDLE: SEE TABLE
7. INSTALLATION TOOL/SETTING: WT197/6-8 (MS90387-2) OR ERG297/5-8

CATALOG NUMBER	MAXIMUM WIRE BUNDLE	A
L-8-120-***	2.000 [50,8]	7.964 [202,29]
L-11-120-***	3.000 [76,2]	11.000 [279,4]
L-11-120FL-***	3.000 [76,2]	11.000 [279,4]
L-14-120-***	4.000 [101,6]	14.284 [362,81]
L-14-120FL-***	4.000 [101,6]	14.284 [362,81]
L-18-120-***	4.875 [123,83]	17.611 [447,32]
L-24-120-***	7.000 [177,8]	23.611 [599,72]
L-28-120-***	8.000 [203,2]	27.611 [701,32]

\* = COLOR CODE- 0= BLACK (OUTDOOR) 4= YELLOW 8= GRAY 17= FLUORESCENT YELLOW  
 1= BROWN 5= GREEN 9= NATURAL 18= FLUORESCENT GREEN  
 2= RED 6= BLUE 11= FLUORESCENT PINK 20= FLUORESCENT BLUE  
 3= ORANGE 7= PURPLE 16= FLUORESCENT ORANGE

\*\* = PACKAGING- C= STD PKG (100) L= STD PKG (50) Q= STD PKG (25)

CONSULT CUSTOMER SERVICE FOR PACKAGE QUANTITY AVAILABILITY

**FLUORESCENT COLORS NOT "UR" OR "CE" RECOGNIZED OR LISTED**

<b>GENERAL NOTES</b>		<b>Thomas &amp; Betts</b> www.tnb.com			
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY. 2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.					
<b>REVISIONS</b>		<b>DESCRIPTION: 8", 11", 14", 18", 24" &amp; 28" SERIES 120 HEAVY DUTY CABLE TIES</b>			
- SEE ERN (****) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****		ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:
		FMM40182 / (2006127)	1 OF 1	-	WSD-000223