



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **L1520CW Conn WT 20A 250V 3PH 3P4W H/L YI** *Eaton Wiring Devices*

Catalog Number	L1520CW
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Watertight Locking Connector, #18-10 Awg, 20A, Industrial, 250V, Back Wiring, Yellow, Steel, Watertight, L15-20, Three-Pole, Four-Wire, Santoprene Thermoplastic Elastomeric, 0.36 to 0.84 In, Ip67
Weight per unit	10.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

dimensions	6.6100 IN X 4.3900 IN X 3.8200 IN
media	Yes

### **Descriptions**

Description	CONN WT 20A 250V 3PH 3P4W H/L YL
extra long description	EWD L1520CW Conn WT 20A 250V 3PH 3P
Features	Eaton's Arrow Hart watertight locking devices utilize a unique, robust design and superior materials to provide watertight security in harsh environments.
Long Description	Eaton Arrow Hart watertight locking connector, #18-10 AWG, 20A, Industrial, 250V, Back wiring, Yellow, Steel, Watertight, L15-20, Three-pole, Four-wire, Santoprene thermoplastic elastomeric, 0.36 to 0.84 in, IP67
Product Type	Conn WT 20A 250V 3PH 3P4W H/L YI
Special Features	Watertight locking

### **Manufacturer Information**

Brand	COOPER WIRING DEVICES
GTIN	00040893642055
Manufacturers Part Number	L1520CW
UPC	040893642055

### **Taxonomies, Classifications, and Categories**

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Watertight

### **Packaging**

Carton	1
Package	10
Weight Per each	10



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Facility - OtherCommercial /  
Institutional Buildings / Structures - Commercial / Institutional  
Buildings / Structures - Other

standard

NOM,UL Listed,CSA certified,cULus Listed,RoHS Compliant