



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1820R R SGL 4W 20A 120/208 T/L

Pass & Seymour/LeGrand

| | |
|------------------|---|
| Catalog Number | L1820R |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Receptacle Single 4-Wire 20A 120/208VOLT Turnlok Registered |
| Weight per unit | 0.2445 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|-----------|
| amperage rating | 20 |
| indoor/outdoor | Indoor |
| Number of Wires | 4 |
| Outlet Type | Locking |
| Phase | 3 |
| Poles | 4-Way |
| Voltage | 120/208 V |
| Voltage Rating | 120/208 |
| Wall Plate Included | NO |
| Wire Size | 18 - 10 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | R SGL 4W 20A 120/208 T/L |
| extra long description | P&S L1820R R SGL 4W 20A 120/208 T/L |
| Features | Impact Resistant, Brass Mounting Strap |
| Long Description | Receptacle Single 4-Wire 20A 120/208Volt Turnlok Registered |
| Product Type | R SGL 4W 20A 120/208 T/L |
| Special Features | Turnlock, locking device, quick thread assembly, rounded back contour, impact & corrosion resistant, new design external cord grips |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007182057 |
| Manufacturers Part Number | L1820-R |
| UPC | 785007182057 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type | RECEPTACLE |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.2445 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------|
| Application | Commercial |
| nema rating | L18-20R |
| standard | UL, UL 498, FEDSPEC |