



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L2N141 2AWG 1/4"BLT 2H 5/8"SPC LNG BRL Cu CMP Lug

Nsi Industries

Catalog Number	L2N141
Manufacturer	Nsi Industries
Description	2 Hole Long Barrel Copper Compression Lug 2 Awg - 1/4" Bolt - 5/8" Mounting Spacing Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. Allows Easy Inspection Of The Termination to Assure Complete Cable Insertion. Tin-Plated to Provide Corrosion and Low Contact Resistance. Marked With Die Index and Color Coded. Listed For 35KV Maximum When Properly Installed. Rated 600V. Culus 486A/B Listed. UL467 Listed On Sizes 6 Awg - 3/0 Awg. Temperature Rating 90 Degrees C.
Weight per unit	4.5 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	# 2 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Brown
Finish	Tin Plated

Dimensions and Weight

Size	L=2.52 - W=.600 - OD=.420 - ID=.310
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	2AWG 1/4"BLT 2H 5/8"SPC LNG BRL CU CMP LUG
extra long description	NSI L2N-141 CMP Lug Cu Long 2 AWG 1
Features	2 Hole Long Barrel Copper Compression Lug 2 AWG - 1/4" Bolt - 5/8" Mounting Spacing Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Long Description	2 Hole Long Barrel Copper Compression Lug 2 AWG - 1/4" Bolt - 5/8" Mounting Spacing Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C.
Product Type	CMP Lug Cu Long 2 Awg 1/4 BLT 5/8 SPC
Special Features	# 2 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing

Manufacturer Information

Brand	Polaris
GTIN	00662381339058
Manufacturers Part Number	L2N-141
UPC	662381339058

Taxonomies, Classifications, and Categories

Type	Long Barrel - Two Hole
------	------------------------

Packaging

Carton	1
Weight Per each	4.5

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)