



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave.  
73108-0000, OK Oklahoma City  
Phone: 405-896-3723  
Fax: 405-272-3057



## **L35048 350MCM 1-Hole Long Barrel Compression Lug 1/2" Bol**

*Nsi Industries*

Catalog Number	L35048
Manufacturer	Nsi Industries
Description	1 Hole Long Barrel Copper Compression Lug 350 MCM - 1/2" Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Low Contact Resistance. Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed and to Cable Manufacturer Instructions. Temperature Rating 90 Degrees C. .
Weight per unit	0.2600 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Cable Size	350 MCM (STR)
Material	Copper
Number of Holes	1
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

### **Material, Color, and Finish**

Color	Red
Finish	Tin Plated

### **Dimensions and Weight**

Size	L=3.46 - W=1.27 - OD=.874 - ID=.701
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave.  
73108-0000, OK Oklahoma City  
Phone: 405-896-3723  
Fax: 405-272-3057

## Descriptions

Description	350MCM 1-HOLE LONG BARREL COMPRESSION LUG 1/2" BOL
extra long description	NSI L35048 CU CMP Lug Long 350 MCM
Features	1 Hole Long Barrel Copper Compression Lug 350 MCM - 1/2" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Long Description	1 Hole Long Barrel Copper Compression Lug 350 MCM - 1/2" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Product Type	Cu CMP Lug Long 350 MCM 1/2 Bolt Size
Special Features	350 MCM (STR) - 1/2 Mounting Hole

## Manufacturer Information

Brand	NSi
GTIN	00662381034151
Manufacturers Part Number	L35048
UPC	662381034151

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - One Hole

## Packaging

Carton	1
Package	12
Weight Per each	0.26

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Hole
standard	UL486A/B