




90VO

Vertical Outside 90° Elbow



Radius R	Rail Height H	A	B
12	4-7	15	15
24		27	27
36		39	39




ITRAY VERTICAL INSIDE ELBOW CATALOG NUMBERING EXAMPLE:					
BOTTOM TYPE	LD - 6	A	- 90 V O	12 - 0	6
VENTED					
LD - Ladder Rung					
VC - Vented Corrugated					
NON-VENTED					
SC - Solid Corrugated					
SB - Solid Bottom					
RAIL HEIGHT	4 - 4"				
	5 - 5"				
	6 - 6"				
	7 - 7"				
MATERIAL		A			
FITTING CODE					
RADIUS					
WIDTH					

- **Material:** Aluminum Alloy 6063 and 5052
- **Finish:** Plain
- **Bottom:** LD: 1" wide rung
SB: Flat sheet over Rung
SC: Solid Corrugated
VC: Vented Corrugated
- **Construction:** Welded
- **Tray Design:** Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126
- **Connectors:** All fittings are supplied with necessary connectors and fasteners
- **Fitting heights (H):** 4", 5", 6", 7"

Legrand
8319 State Route 4
Mascoutah, IL 62258 USA
800-658-4641
618-566-3230
Fax 618-566-3250
www.legrand.us/cablofil

90VO

Vertical Outside 90° Elbow



Radius R	Rail Height H	A	B
12	4-7	15	15
24		27	27
36		39	39

ITRAY VERTICAL INSIDE ELBOW CATALOG NUMBERING EXAMPLE:					
BOTTOM TYPE	LD - 6	A	- 90 V O	12 - 0	6
VENTED					
LD - Ladder Rung					
VC - Vented Corrugated					
NON-VENTED					
SC - Solid Corrugated					
SB - Solid Bottom					
RAIL HEIGHT	4 - 4"				
	5 - 5"				
	6 - 6"				
	7 - 7"				
MATERIAL		A			
FITTING CODE					
RADIUS					
WIDTH					

- **Material:** Aluminum Alloy 6063 and 5052
- **Finish:** Plain
- **Bottom:** LD: 1" wide rung
SB: Flat sheet over Rung
SC: Solid Corrugated
VC: Vented Corrugated
- **Construction:** Welded
- **Tray Design:** Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126
- **Connectors:** All fittings are supplied with necessary connectors and fasteners
- **Fitting heights (H):** 4", 5", 6", 7"