



# ESSENTIAL SERIES

GENERAL PURPOSE LED BULBS

## KT-LED11.5BR40-8XX

REPLACEMENT LAMP

### DESCRIPTION

11.5W BR40 Lamp | 2700–5000K | >80 CRI | Standard Flood



RoHS Compliant

2 YEAR WARRANTY

<b>LAMP TYPE:</b> BR40
<b>BASE TYPE:</b> E26 (Medium)
<b>WATTAGE:</b> 11.5W
<b>COLOR TEMPERATURE:</b> 2700–5000K
<b>COLOR RENDERING INDEX (CRI):</b> >80
<b>WARRANTY:</b> 2 Years
<b>RATED LIFE:</b> L70 (15,000 Hours)



### TYPICAL APPLICATIONS

- Recessed Downlights
- Track Lighting
- Surface Mount Ceiling Fixtures

### PRODUCT FEATURES

- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- Durable Plastic housing lowers the risk for breakage
- Smooth diffused lens for comfortable glare free performance
- Smooth, uniform dimming
- Operating temperature range –4°F/–20°C to 95°F/35°C
- Long Life minimizes replacement and maintenance costs
- ANSI complaint construction ensures fitment for intended applications
- Meets Energy Star requirements
- UL Listed


### ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Light Distribution	Dimmable	Efficacy
KT-LED11.5BR40-827	BR40 bulb. Standard flood, dimmable	2700K	120V	11.5W	75W/65W halogen	E26	940	>80	110°	Yes	82 lm/W
KT-LED11.5BR40-830	BR40 bulb. Standard flood, dimmable	3000K	120V	11.5W	75W/65W halogen	E26	940	>80	110°	Yes	82 lm/W
KT-LED11.5BR40-840	BR40 bulb. Standard flood, dimmable	4000K	120V	11.5W	75W/65W halogen	E26	940	>80	110°	Yes	82 lm/W
KT-LED11.5BR40-850	BR40 bulb. Standard flood, dimmable	5000K	120V	11.5W	75W/65W halogen	E26	940	>80	110°	Yes	82 lm/W

## KT-LED11.5BR40-8XX

### REPLACEMENT LAMP

#### PHYSICAL CHARACTERISTICS



#### PACKAGING

Carton Quantity	6 pcs
Carton Dimensions	14.88" × 10.08" × 7.6"
Carton Weight	4.52 lbs

#### LAMP DIMENSIONS

A (Length)	6.22"
B (Diameter)	4.92"

BASE TYPE: E26 (Medium)

#### ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	ITEM STATUS
KT-LED11.5BR40-8XX	6 pcs	Active

#### CATALOG NUMBER BREAKDOWN

## KT-LED11.5BR40-8XX

1 2 3 4 5 6

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 800 Series
- 6 Color Temperature