



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road
70665-0000, LA Sulphur
Phone: 337-533-8019
Fax: 337-533-8055



LED21T848P2S84 4' 21W Led Signhero 40K 360 Deg BLST Bypass

Keystone Technologies

Catalog Number	LED21T848P2S84
Manufacturer	Keystone Technologies
Description	Led Sign Lamp, Linear, Double Sided Type; 48 Inch; UI 48/879A, UI (Canada and Us), Sam Approval; Single or Double Sided Outdoor Signage Application; 120 to 277 Volt Voltage Rating; 1.1 Inch Diameter; 21 Watt Wattage; Led Sign Tube
Weight per unit	0.3900 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Beam Spread Angle	360 Degree
Intensity	2500 Lumen
Item	LED Sign Tube
Voltage Rating	120 to 277 Volt
Wattage	21 Watt

Material, Color, and Finish

Base Material	Plastic
Base Type	R17d Rotatable
Color Rendering Index	80 A
Color Temperature in Kelvin	4000

Dimensions and Weight

Diameter	1.1 Inch
Length	48 INCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road
70665-0000, LA Sulphur
Phone: 337-533-8019
Fax: 337-533-8055

Descriptions

Additional Information	Efficacy 119 Lumen per Watt; Operating Temperature -22 to 131 Deg F
Commodity Description	LED SPECIALTY LAMPS & MODULES
Description	4' 21W LED SIGNHERO 40K 360 DEG BLST BYPASS
extra long description	LINEAR, DOUBLE SIDED TYPE; 48 INCH; UL 48/879A, UL (CANADA AND US), SAM APPROVAL; SINGLE OR DOUBLE SIDED OUTDOOR SIGNAGE APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1.1 INCH DIAMETER; 21 WATT WATTAGE; LED SIGN TUBE; R17D ROTATABLE BASE TYPE; 50000 LIFE IN HOUR; PLASTIC BASE MATERIAL; 2500 LUMEN INTENSITY; 4000; 80 COLOR RENDERING INDEX; 360 DEGREE BEAM SPREAD ANGLE; SIGN HERO BRAND; EFFICACY 119 LUMEN PER WATT; OPERATING TEMPERATURE -22 TO 131 DEG F; 800 MODEL
Long Description	LED SIGN LAMP, LINEAR, DOUBLE SIDED TYPE; 48 INCH; UL 48/879A, UL (CANADA AND US), SAM APPROVAL; SINGLE OR DOUBLE SIDED OUTDOOR SIGNAGE APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 1.1 INCH DIAMETER; 21 WATT WATTAGE; LED SIGN TUBE
Product Type	Led Sign Lamp

Manufacturer Information

Brand	Keystone Technologies
GTIN	00843654132235
Manufacturers Part Number	KT-LED21T8-48P2S-840-D /G2
Model	800
UPC	843654132235

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	Linear, Double Sided

Packaging

Carton	1
Package	9
Weight Per each	0.39

Uses, Certifications, and Standards

Application	Single or Double Sided Outdoor Signage
Approval	UL 48/879A, UL (Canada and US), SAM