



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street  
66046-0000, KS Lawrence  
Phone: 785-330-9441  
Fax: 785-371-0291



## **LED9T824G840X3 \*Delisted\* 9W Led T8 24" 40K Combo DBL/SNGL or BLS** *Keystone Technologies*

Catalog Number	LED9T824G840X3
Manufacturer	Keystone Technologies
Description	9W T8 Led Tube, Ballast Compatible & 120-277V Line Voltage Compatible (Single or Double Ended Wiring) 2FT, 4000K, Combodrive X3
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	120-277V OR Ballast Dependent
ip rating	N/A
Lamp Type	T8
lumens	1400
Nominal Length	24 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	N/A
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	Frosted Glass
Description	9W LED T8 24" 40K COMBO DBL/SNGL ENDED OR BALLAST
extra long description	Key KT-LED9T8-24G-840-X3 9W T8 LED
Long Description	9W T8 LED Tube, Ballast Compatible & 120-277V Line Voltage Compatible (Single OR Double Ended Wiring) 2ft, 4000K, ComboDrive X3
Product Type	9W T8 Led Tube, Ballast Compatible & 120-277V Line Voltage C



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street  
66046-0000, KS Lawrence  
Phone: 785-330-9441  
Fax: 785-371-0291

## Manufacturer Information

Brand	Keystone
GTIN	00843654134178
Manufacturers Part Number	KT-LED9T8-24G-840-X3
UPC	843654134178

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.4

## Uses, Certifications, and Standards

Energy Star	N
-------------	---