LF3-TR



LF3-15-TR



LF3-30-TR



LF3-50-TR



LF THREAD

1/2" strain-relief connector for TR series up to 50W


TECHNICAL SPECIFICATIONS:

:: Housing: Die-cast aluminum housing with powder coat finish (Dark Bronze or White)
:: Philips Lumileds Lexeon 3030 high flux LED
:: TIR optic lens - TYPE II
:: 18" SJTW 18/3 AWG cable
:: Voltage: 120~277V; 60Hz AC
:: Operating Temp:-4°F to 104°F
:: Up to 110 lumens per watt
:: CRI: 82~84
:: Beam Angle: 104°
:: 70,000 hour rated life
:: 7-year warranty
:: Suitable for Wet Locations, IP65
:: Solid state lighting technology for long life, no maintenance needed and high-efficiency

APPLICATIONS:

:: Ideal for general site lighting, alleys, loading docks, doorway, pathway and parking areas.
:: Replace existing HID flood lights/ wall packs
:: Great for use with motion sensors or other instant on/off controls





LF3 FLOOD LIGHT SERIES WITH TRUNNION

CATALOG NO.		WATTS	LUMENS	COLOR TEMP	REPLACEMENT RANGE	DIMENSIONS
BRONZE	WHITE					
LF3-15CW-TR	-	15W	1600LM	5000K	50~70 MH	4-1/4"(W) x 3-1/7"(H) x 1-1/2"(D)
LF3-15WW-TR	-	15W	1500LM	3000K	50~70 MH	
LF3-30CW-TR	-	30W	3500LM	5000K	70~100 MH	6-3/4"(W) x 5-1/8"(H) x 1-3/5"(D)
LF3-30WW-TR	LF3-WH-30WW-TR	30W	3400LM	3000K	70~100 MH	
LF3-50CW-TR	-	50W	6000LM	5000K	100~175 MH	8-1/2"(W) x 6"(H) x 1-4/5"(D)
LF3-50WW-TR	-	50W	5600LM	3000K	100~175 MH	
LF-THREAD	1/2" hub adaptor for fixtures with trunnion bracket (on fixtures up to 50W)					

LF3-TR



LF3-15-TR



LF3-30-TR



LF3-50-TR



LF THREAD

1/2" strain-relief connector for TR series up to 50W


TECHNICAL SPECIFICATIONS:

:: Housing: Die-cast aluminum housing with powder coat finish (Dark Bronze or White)
:: Philips Lumileds Lexeon 3030 high flux LED
:: TIR optic lens - TYPE II
:: 18" SJTW 18/3 AWG cable
:: Voltage: 120~277V; 60Hz AC
:: Operating Temp:-4°F to 104°F
:: Up to 110 lumens per watt
:: CRI: 82~84
:: Beam Angle: 104°
:: 70,000 hour rated life
:: 7-year warranty
:: Suitable for Wet Locations, IP65
:: Solid state lighting technology for long life, no maintenance needed and high-efficiency

APPLICATIONS:

:: Ideal for general site lighting, alleys, loading docks, doorway, pathway and parking areas.
:: Replace existing HID flood lights/ wall packs
:: Great for use with motion sensors or other instant on/off controls





LF3 FLOOD LIGHT SERIES WITH TRUNNION

CATALOG NO.		WATTS	LUMENS	COLOR TEMP	REPLACEMENT RANGE	DIMENSIONS
BRONZE	WHITE					
LF3-15CW-TR	-	15W	1600LM	5000K	50~70 MH	4-1/4"(W) x 3-1/7"(H) x 1-1/2"(D)
LF3-15WW-TR	-	15W	1500LM	3000K	50~70 MH	
LF3-30CW-TR	-	30W	3500LM	5000K	70~100 MH	6-3/4"(W) x 5-1/8"(H) x 1-3/5"(D)
LF3-30WW-TR	LF3-WH-30WW-TR	30W	3400LM	3000K	70~100 MH	
LF3-50CW-TR	-	50W	6000LM	5000K	100~175 MH	8-1/2"(W) x 6"(H) x 1-4/5"(D)
LF3-50WW-TR	-	50W	5600LM	3000K	100~175 MH	
LF-THREAD	1/2" hub adaptor for fixtures with trunnion bracket (on fixtures up to 50W)					