

Specifications

Eaton LGHMVD24BX



Photo is representative

General specifications

PRODUCT NAME	Eaton molded case circuit breaker accessory handle mechanism
CATALOG NUMBER	LGHMVD24BX
UPC	786685293745
PRODUCT LENGTH/DEPTH	26 in
PRODUCT HEIGHT	12.5 in
PRODUCT WIDTH	11.5 in
PRODUCT WEIGHT	6 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	Contact Manufacturer
GLOBAL CATALOG	LGHMVD24BX
PRODUCT TYPE	Molded case circuit breaker accessory

Product specifications

USED WITH	LG-frame
FRAME SIZE	Frame LG
SERIES	Series G
HANDLE COLOR	Black, blue
HANDLE LENGTH	24 in
NEMA RATING	NEMA 4, NEMA 4X
SHAFT LENGTH	24 in
TYPE	S2 Handle mechanism

Resources

APPLICATION NOTES

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Motor protection circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

BROCHURES

[Series G MCCB quick selector](#)

[Current limiting molded case circuit breaker module product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

MULTIMEDIA

[Flex shaft handle installation tutorial](#)

SPECIFICATIONS AND DATASHEETS

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - LGHMVD24BX](#)

[NG and ND-Frame molded case circuit breakers](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton LGHMVD24BX



Photo is representative

General specifications

PRODUCT NAME	Eaton molded case circuit breaker accessory handle mechanism
CATALOG NUMBER	LGHMVD24BX
UPC	786685293745
PRODUCT LENGTH/DEPTH	26 in
PRODUCT HEIGHT	12.5 in
PRODUCT WIDTH	11.5 in
PRODUCT WEIGHT	6 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	Contact Manufacturer
GLOBAL CATALOG	LGHMVD24BX
PRODUCT TYPE	Molded case circuit breaker accessory

Product specifications

USED WITH	LG-frame
FRAME SIZE	Frame LG
SERIES	Series G
HANDLE COLOR	Black, blue
HANDLE LENGTH	24 in
NEMA RATING	NEMA 4, NEMA 4X
SHAFT LENGTH	24 in
TYPE	S2 Handle mechanism

Resources

APPLICATION NOTES

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Motor protection circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

BROCHURES

[Series G MCCB quick selector](#)

[Current limiting molded case circuit breaker module product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

MULTIMEDIA

[Flex shaft handle installation tutorial](#)

SPECIFICATIONS AND DATASHEETS

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - LGHMVD24BX](#)

[NG and ND-Frame molded case circuit breakers](#)

WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

