



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LMVS2TW100GPMT 100W HPS FX *Crouse-Hinds*

Catalog Number	LMVS2TW100GPMT
Manufacturer	Crouse-Hinds
Description	Abbinstall DSM10P120TGCB2 Appleton MLWL102G1GMT Crouse LMVS2TW100GP120 Killark MBL100GGB2 Killark MBL101GGB2 Raco HLMBL100GGB2 Raco HLMBL101GGB2 Thomasbett DSM10P120TGCB2
Weight per unit	19.8 (lbs/each)
Product Category	Boxes & Covers

Features

amperage rating	Eaton Crouse-Hinds
Attachment Type	Electrogalvanized Steel
connection	Ind Facilities & Factories - Facility: Safety and Security Systems
Cord Type	Eaton Crouse-Hinds
Lamp Type	HIGH PRESSURE SODIUM
Voltage Rating	120/208/240/277
Wattage	100

Material, Color, and Finish

Backing Material	Electrogalvanized Steel
Color	Eaton Crouse-Hinds

Dimensions and Weight

Length	Feraloy Iron Alloy Body and Gland Nut
--------	---------------------------------------

Descriptions

Description	100W HPS FX
Long Description	ABBInstall DSM10P120TGCB2 Appleton MLWL102G1GMT Crouse LMVS2TW100GP120 Killark MBL100GGB2 Killark MBL101GGB2 Raco HLMBL100GGB2 Raco HLMBL101GGB2 ThomasBett DSM10P120TGCB2
Product Type	100W HPS 3/4 120V MT Wall
Special Features	With Globe and Guard, 3/4 In Hub

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274835693
Manufacturers Part Number	LMVS2TW100GP/MT
sub brand	Ind Facilities & Factories - Facility: Power Distribution and Control
UPC	782274835693



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION LIGHTING FIXTURES
Type	Luminaire, Multi Tap

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	19.75

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
Enclosure	Feraloy Iron Alloy Body and Gland Nut
Mounting	Wall, Thru-Feed
standard	UL 844, UL 1598, UL 1598A, CSA C22.2