



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LP3P012048R LP3P-012-048R

Federal Signal Corp.

| | |
|------------------|---|
| Catalog Number | LP3P012048R |
| Manufacturer | Federal Signal Corp. |
| Description | Streamline Low Profile Strobe Light, 12-48VDC, NPT Pipe Mount, Red - Available In 12-48VDC, 120VAC and 240VAC, LP3E Available In 120VAC Only. Surface Mount (S), Edison Mount (E), T-Mount (T), Integrated 1/2-Inch NPT Pipe Mount (P) or 1/2-Inch NPT Male Pipe Mount (M). Five Lens Colors: Amber, Blue, Clear, Green and Red. Screw-On Lens Provides Easy Access. Conformal Coated PCB. Type 4X, IP66 Enclosure. IP69K Compliant (Excludes Models LP3E and LP3T). PLC and Triac Compatible. Csa Certified. UI and Cul List |
| Weight per unit | 0.5300 (lbs/each) |
| Product Category | Bells, Horns, Sirens, BZZRS, S |

Features

| | |
|-----------------|---------------|
| amperage rating | 0.44-0.10 |
| average life | 4,000 |
| Light Source | Strobe Tube |
| Material | Polycarbonate |
| Shape | Cylindrical |
| Voltage Rating | 12-48VDC |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Red |
| Style | Strobe |

Dimensions and Weight

| | |
|------|--------------------------|
| Size | 5.82 H x 3.13 W x 3.13 D |
|------|--------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | LP3P-012-048R |
| extra long description | FED-SIG LP3P-012-048R STROBE PIPE M |
| Long Description | StreamLine Low Profile Strobe Light, 12-48VDC, NPT Pipe Mount, Red - Available in 12-48VDC, 120VAC and 240VAC, LP3E available in 120VAC only. Surface mount (S), Edison mount (E), T-mount (T), integrated 1/2-inch NPT pipe mount (P) or 1/2-inch NPT male pipe mount (M). Five lens colors: Amber, Blue, Clear, Green and Red. Screw-on lens provides easy access. Conformal coated PCB. Type 4X, IP66 enclosure. IP69K compliant (excludes models LP3E and LP3T). PLC and triac compatible. CSA Certified. UL and cUL List |
| Product Type | Strobe Pipe Mount 12-48VDC Red |
| Special Features | PLC And Triac Compatible |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Federal Signal |
| GTIN | 00782979203315 |
| Manufacturers Part Number | LP3P-012-048R |
| Model | LP3P |
| UPC | 782979203315 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | SIGNALING EQUIPMENT |
| Type | LOW PROFILE STROBE LIGHT |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.53 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------------------------|
| Application | Indoor/Outdoor |
| environmental conditions | -31 to 150 |
| Mounting | 1/2-Inch NPT Pipe |
| nema rating | Type 4X, IP66, IP69K Enclosure |
| standard | UL Listed/cUL Listed/CSA Certified |