

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton 75604-0000, TX Longview Phone: 903-757-8491 Fax: 903-758-0441



LPJ35SP 35A 600V TD Dual Elem Class J Fuse Bussmann Fuses

Catalog Number	LPJ35SP
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series LPJ Fuse, Bussmann Series Class J Fuse, LPJ, Time-Delay, Dual-Element Current Limiting Fuse, 35 A, Non-Idicating Fuse, Interrupting Rating Of 300 Ka At 600 Vac and 100 Ka At 300 VDC
Weight per unit	0.1900 (lbs/each)
Product Category	Dual Element
atures	
dimensions	2.3800 IN X 1.0600 IN X 1.0600 IN
media	Yes
escriptions	
Description	35A 600V TD DUAL ELEM CLASS J FUSE
extra long description	BUSS LPJ-35SP BUSSMAN FUSE (55
Features	Bussmann's UL Class J fuse products extend both our Low-Peak family of products with our LPJ_SP and LPJ_SPI dual-element, time-delay fuses as well as our Limitron line offering fast-acting JKS fuses. The LPJ fuses provide industry leading 300,000 amp interrupting rating at 600Vac RMS Sym and 100kA Vdc while delivering a minimum of 10 seconds of 500 percent rated curren ride-through performance which is ideal for sizing of high inrush loads. The LPJ products are available with optional permanent replace fu
Long Description	Eaton Bussmann series LPJ fuse, Bussmann Series Class J fuse, LPJ, time-delay, dual-element current limiting fuse, 35 A, non-idicating fuse, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc
Product Type	Bussman Fuse (55
anufacturer Information	
Brand	Eaton
GTIN	00051712523325
Manufacturers Part Number	LPJ-35SP
UPC	051712523325

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton 75604-0000, TX Longview Phone: 903-757-8491 Fax: 903-758-0441

Packaging	
Carton	10
Weight Per each	0.19
Uses, Certifications, and Standards	
Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	UL Listed ,CSA Certified,RoHS Compliant