



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LS880L35K10VEB14 Led LT FX

Cree Lighting Usa LLC

Catalog Number	LS880L35K10VEB14
Manufacturer	Cree Lighting Usa LLC
Description	00810048027477 0810048 810048027477 81004802747 02747 LS8 80L 35K 10V EB14 LS880L35K10VEB14 LS8-80L-35K-10V-EB14 LS8 Surface Ambient, 80L, 35K, 10V, Eb Crea LS8 80L 35K 10V EB14 Crea LS880L35K10VEB14 Crea LS8-80L-35K-10V-EB14 Cree Lighting LS8 80L 35K 10V EB14 Cree Lighting LS880L35K10VEB14 Cree Lighting LS8-80L-35K-10V-EB14 Cree LS8 80L 35K 10V EB14 Cree LS880L35K10VEB14 Cree LS8-80L-35K-10V-EB14 Crie LS8 80L 35K 10V EB14 Crie LS880L35K10VEB14 Crie LS8-80L-35K-10V-EB14 39112102 4046 Light Emitting Diode L
Weight per unit	15.4 (lbs/each)
Product Category	Lighting

Features

average life	50000
Lamp Type	LED
lumens	8k
media	Yes
Voltage Rating	120 to 277
Wattage	88

Material, Color, and Finish

Color	3500
-------	------

Dimensions and Weight

Size	96 IN Length X 2.5 IN Width X 3.0 IN Height
------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	LED LT FX
extra long description	Cree Light LS8-80L-35K-10V-EB14 LS8
Long Description	00810048027477 0810048 810048027477 81004802747 02747 LS8 80L 35K 10V EB14 LS880L35K10VEB14 LS8-80L-35K-10V-EB14 LS8 Surface Ambient, 80L, 35K, 10V, EB Crea LS8 80L 35K 10V EB14 Crea LS880L35K10VEB14 Crea LS8-80L-35K-10V-EB14 Cree Lighting LS8 80L 35K 10V EB14 Cree Lighting LS880L35K10VEB14 Cree Lighting LS8-80L-35K-10V-EB14 Cree LS8 80L 35K 10V EB14 Cree LS880L35K10VEB14 Cree LS8-80L-35K-10V-EB14 Crie LS8 80L 35K 10V EB14 Crie LS880L35K10VEB14 Crie LS8-80L-35K-10V-EB14 39112102 4046 Light emitting diode L
Product Type	LS8 Surface Ambient, 80L, 35K, 10V, Eb
Special Features	8 FT LED Surface Ambient Luminaire, Utilizes Cree TrueWhite Technology; Constructed of durable 22 gauge steel; Acrylic lens delivers a low-glare, diffused light distribution; Prepainted white for enhanced smooth finish; Unique combination of reflective and refractive optical components achieves a uniform, comfortable appearance while eliminating pixelation and color fringing; Components work together to optimize distribution, balancing the delivery of high illuminance levels on horizontal surfaces with an

Manufacturer Information

Brand	Cree Led Lighting Solutio
GTIN	00810048027477
Manufacturers Part Number	LS880L35K10VEB14
sub brand	LS8
UPC	810048027477

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	LS8 Series Surface Ambient

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	15.3999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Auto Dealership, Corporate Campus, Education, Government,
Healthcare, Industrial And Warehouse, Restaurants And
Hospitality, Retail And Grocery, Petroleum And Convenience
Store

Mounting
standard

Surface, suspended, pendant, cove
C/US UL Listed, DLC Qualified