



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LSF25KNPC 11/15/22/25W Led Flood 3K/4K/5K Knuckle Mount

Cooper Lighting Solutions

Catalog Number	LSF25KNPC
Manufacturer	Cooper Lighting Solutions
Description	LSF Floodlight, CCT Selectable 3000K-4000K-5000K, 70 Cri, 120-347V, 50-60 HZ, Selectable Lumens 1700-2500-3500-4000 / 11-15-22-25W, Selectable Dusk-to-Dawn Button-Type Photocontrol, Knuckle.
Weight per unit	2.1 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.072A @347V
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	1700-2500-3500-4000
Voltage Rating	120-347V

Dimensions and Weight

Size	8.54 IN Length 2.0 IN Width 9.65 IN Height
------	--

Descriptions

Description	11/15/22/25W LED FLOOD 3K/4K/5K KNUCKLE MOUNT
extra long description	CLS LSF25-KN-PC CCT SELECT FLOOD, 2
Long Description	LSF Floodlight, CCT Selectable 3000K-4000K-5000K, 70 CRI, 120-347V, 50-60 Hz, Selectable Lumens 1700-2500-3500-4000 / 11-15-22-25W, Selectable Dusk-to-Dawn Button-type photocontrol, Knuckle.
Product Type	CCT Select Flood, 25W, KNC, PC
Special Features	Available in 3 housing sizes and multiple lumen packages

Manufacturer Information

Brand	LUMARK
GTIN	00080083267705
Manufacturers Part Number	LSF25-KN-PC
UPC	080083267705

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	2.14



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	KNUCKLE
standard	ISO Certified;DLC Qualified;1.5G Vibration Rated;FCC Class A;IP65 Rated;UL Listed;RoHS Compliant