



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253



LSF65YKPC 25/35/45/65W Led Flood 3K/4K/5K Yoke Mount

Cooper Lighting Solutions

Catalog Number	LSF65YKPC
Manufacturer	Cooper Lighting Solutions
Description	LSF Floodlight, CCT Selectable 3000K-4000K-5000K, 70 Cri, 120-347V, 50-60 HZ, Selectable Lumens 9000-12, 000-15, 000-20, 000 / 50-70-90-120W, Selectable Dusk-to-Dawn Button-Type Photocontrol, Yoke
Weight per unit	3.9 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.187A @347V
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	5000-6500-8000-10000
Voltage Rating	120-347V

Dimensions and Weight

Size	10.35 IN Length 2.17 IN Width 11.1 IN Height
------	--

Descriptions

Description	25/35/45/65W LED FLOOD 3K/4K/5K YOKE MOUNT
extra long description	CLS LSF65-YK-PC CCT SELECT FLOOD, 6
Long Description	LSF Floodlight, CCT Selectable 3000K-4000K-5000K, 70 CRI, 120-347V, 50-60 Hz, Selectable Lumens 9000-12,000-15,000-20,000 / 50-70-90-120W, Selectable Dusk-to-Dawn Button-type photocontrol, Yoke
Product Type	CCT Select Flood, 65W, Yk, PC
Special Features	Available in 3 housing sizes and multiple lumen packages

Manufacturer Information

Brand	LUMARK
GTIN	00080083267781
Manufacturers Part Number	LSF65-YK-PC
UPC	080083267781

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	3.86



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253

Uses, Certifications, and Standards

Application	lighting
Mounting	YOKE
standard	ISO Certified;DLC Qualified;1.5G Vibration Rated;FCC Class A;IP65 Rated;UL Listed;RoHS Compliant