



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106



LSF25KNYKPC 11/15/22/25W Led Flood 3K/4K/5K Yoke & KNKL MNT *Cooper Lighting Solutions*

Catalog Number	LSF25KNYKPC
Manufacturer	Cooper Lighting Solutions
Description	LSF Floodlight, Slipfitter and Trunnion, Selectable CCT: 3000K/4000K/5000K, Selectable Lumens: 1700-2500-3500-4000, 25W, 70 Cri, 120-347V, 50-60 HZ, Dusk-to-Dawn Via Button-Type Photocontrol
Weight per unit	2.3 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.07A at 347V
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	4000
Voltage Rating	120-347V

Dimensions and Weight

Size	8.64 IN Length 2.15 IN Width 10.81 IN Height
------	--

Descriptions

Description	11/15/22/25W LED FLOOD 3K/4K/5K YOKE & KNKL MNT
extra long description	CLS LSF25-KNYK-PC CCT SELECT FLOOD,
Long Description	LSF Floodlight, Slipfitter and Trunnion, Selectable CCT: 3000K/4000K/5000K, Selectable Lumens: 1700-2500-3500-4000, 25W, 70 CRI, 120-347V, 50-60 Hz, Dusk-to-Dawn via Button-type photocontrol
Product Type	CCT Select Flood, 25W, KNC & Yoke, PC
Special Features	Available in selectable CCT and selectable lumens

Manufacturer Information

Brand	LUMARK INDOOR
GTIN	00080083305230
Manufacturers Part Number	LSF25-KNYK-PC
UPC	080083305230

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	2.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106

Uses, Certifications, and Standards

Application	lighting
Mounting	Knuckle/Yoke
standard	ISO Certified;DLC Qualified;1.5G Vibration Rated;FCC Class A;IP65 Rated;UL Listed;RoHS Compliant