



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street  
72701-0000, AR Fayetteville  
Phone: 479-443-4948  
Fax: 479-443-6465



## LTC0751 3/4" Xtraflex LT Orange

Abb Installation Products, Inc

Catalog Number	LTC0751
Manufacturer	Abb Installation Products, Inc
Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved For Direct Burial In The Us, UI Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Csa Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Orange With Black Markings
Weight per unit	0.1850 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

Inside Diameter	0.8189
outside diameter	1.0512
Voltage Rating	600 V

### Material, Color, and Finish

Color	Orange
-------	--------

### Dimensions and Weight

Length	1200.7874
--------	-----------

### Descriptions

Also Known As...	Liquid Tight Conduit Carflex®
Description	3/4" XTRAFLEX LT ORANGE
extra long description	ABB LTC075-1 3/4IN LT TYPE B COND P
Long Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved for Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Orange with Black Markings
Product Type	3/4IN LT Type B Cond PVC Org
similar brands	Sealtite®
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily

### Manufacturer Information

Brand	T&B Ind Fitting
GTIN	00786210700786
Manufacturers Part Number	LTC075-1
UPC	786210700786



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street  
72701-0000, AR Fayetteville  
Phone: 479-443-4948  
Fax: 479-443-6465

## Taxonomies, Classifications, and Categories

Category Description ..... NON-METALLIC SEALTITE AND FITTINGS

Type ..... Liquidtight Flexible Non-Metallic Conduit

## Trade Size

Trade Size ..... 3/4 in

## Packaging

Carton ..... 100

Weight Per foot ..... 0.185

## Uses, Certifications, and Standards

Application ..... Machine Tools, Motor Hookups, Food Processing Equipment,  
Extensions from Wire Ways, and Sensor and Micro Switch Wiring  
Found In Control Consoles

standard ..... UL E95745, CSA