



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LTC075 3/4" PVC Smooth NM LT Conduit

Abb Installation Products, Inc

Catalog Number	LTC075
Manufacturer	Abb Installation Products, Inc
Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved For Outdoor and Direct Burial In The Us, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Csa Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black With Orange Markings
Weight per unit	0.2160 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Inside Diameter	0.81890
outside diameter	1.05120
Voltage Rating	600 V

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Length	1.20080
--------	---------

Descriptions

Also Known As...	Carflex®
	Liquid Tight Conduit
Description	3/4" PVC SMOOTH NM LT CONDUIT
extra long description	ABB LTC075 3/4IN LT TYPE B COND PVC
Long Description	Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings
Product Type	3/4IN LT Type B Cond PVC BLK
similar brands	Sealtite®
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily

Manufacturer Information

Brand	T&B Ind Fitting
GTIN	00786210789552
Manufacturers Part Number	LTC075
UPC	786210789552



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	NON-METALLIC SEALTITE AND FITTINGS
Type	Liquidtight Flexible Non-Metallic Conduit

Trade Size

Trade Size	3/4 in
------------	--------

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per foot	0.216

Uses, Certifications, and Standards

Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles
standard	UL E95745, CSA