



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DGHR Non-III Mom PB Guarded Extd Red *Eaton Corp*

Catalog Number	M22DGHR
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM Modular Pushbutton Operator, RQM-Titan, Extended, Red Actuator, Silver Bezel, Non-Illuminated, 5, 000, 000 Operations, Momentary, Guarded, M22 Series
Weight per unit	0.0300 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Extended with guard, Button
dimensions	7.0000 IN X 5.0000 IN X 1.5000 IN
operating cycles	5 million

Dimensions and Weight

Depth	7.0000
Height	1.5000
Size	22.5 mm
Width	5.0000

Descriptions

Description	NON-ILL MOM PB GUARDED EXTD RED
extra long description	ETN M22-DGH-R NON-ILL MOM PB GUARDE
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton 22.5 mm Modular Pushbutton Operator, RQM-Titan, Extended, Red Actuator, Silver bezel, Non-illuminated, 5,000,000 operations, Momentary, Guarded, M22 Series
Product Type	Non-III Mom PB Guarded Extd Red

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685275147
Manufacturers Part Number	M22-DGH-R
Model	Modular pushbutton
UPC	786685275147



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....MINATURE PILOT DEVICES.22MM

Type.....Modular pushbutton

Packaging

Carton.....1

Weight Per each.....0.03

Uses, Certifications, and Standards

Application.....Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

environmental conditions.....IP67, IP69K, NEMA 4X, NEMA 13

standard.....CCC Marked,Lloyd's Register Certified,CSA

Certified,GoST-R,Bureau Veritas,CE Marked