



M22DGK11P Green FL Mom PB 1NO/1NC LGND PLS Pop

Eaton Corp

Catalog Number	M22DGK11P
Manufacturer	Eaton Corp
Description	Eaton 22.5 MM RMQ-Titan Pushbutton, Etching: No, Early Make, Green Actuator, Silver Bezel, 1NO - 1NC, IP67, IP69K, Non-Illuminated, Flush Mounting, Nema 4X, 13 and 5,000,000 Operations, Momentary, 22.5 MM, Flush Pushbutton, M22
Weight per unit	0.0800 (lbs/each)
Product Category	Push Button Complete Assembly

Features

action	Green
actuator	Button, Flush
Contact Configuration	1 NO-1 NC
operating cycles	5 million

Dimensions and Weight

Depth	0.5
Height	4
Size	22.5 mm
Width	5

Descriptions

Description	GREEN FL MOM PB 1NO/1NC LGND PLS POP
extra long description	ETN M22-D-G-K11-P GREEN FL MOM PB,
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton 22.5 mm RMQ-Titan Pushbutton, Etching: NO, early make, Green Actuator, Silver bezel, 1NO - 1NC, IP67, IP69K, Non-Illuminated, Flush mounting, NEMA 4X, 13 and 5,000,000 operations, Momentary, 22.5 mm, Flush Pushbutton, M22
Product Type	Green FL Mom PB, 1NO/1NC, LGND PLS Pop



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street
88201-0000, NM Roswell
Phone: 575-208-1571
Fax: 575-208-1572

Manufacturer Information

Brand	Eaton
GTIN	00786685382531
Manufacturers Part Number	M22-D-G-K11-P
Model	Modular pushbutton
UPC	786685382531

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------

Packaging

Carton	1
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
Mounting	FLUSH
standard	CCC Marked,Lloyd's Register Certified,CSA Certified,Bureau Veritas,CE Marked,GoST-R