



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DHRK11P Red Ext Mom PB 1NO/1NC LGND PLS Pop *Eaton Corp*

Catalog Number	M22DHRK11P
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton M22 Pushbutton, Complete Device, 22.5 MM, Extended, Momentary, Non-Illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, Nema 4X
Weight per unit	0.0800 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Button, Extended
Contact Configuration	1 NO-1 NC

Dimensions and Weight

Depth	0.5
Height	4
Size	22.5 mm
Width	5

Descriptions

Description	RED EXT MOM PB 1NO/1NC LGND PLS POP
extra long description	ETN M22-DH-R-K11-P RED EXT MOM PB,
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton M22 Pushbutton, Complete Device, 22.5 mm, Extended, Momentary, Non-illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, NEMA 4X
Product Type	Red Ext Mom PB, 1NO/1NC, LGND PLS Pop

Manufacturer Information

Brand	Eaton
GTIN	00786685382524
Manufacturers Part Number	M22-DH-R-K11-P
Model	Modular pushbutton
UPC	786685382524

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
standard	CSA Certified,Lloyd's Register Certified,CCC Marked,CE Marked,GoST-R,Bureau Veritas