



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



M22LGGP Green Indicating Light 12-30VAC/DC Led LGND PLS Po *Eaton Corp*

Catalog Number	M22LGGP
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Complete Indicating Light, Flush, IP67, IP69K, Nema 4X, 13, Illuminated, Green Lens, 100,000 Hours Of Operation, 12-30 Vac/DC
Weight per unit	0.0500 (lbs/each)
Product Category	Pilot Light Complete Assemblie

Features

dimensions	2.0000 IN X 4.0000 IN X 1.0000 IN
Voltage Rating	12-30 Vac/dc

Dimensions and Weight

Size	22.5 mm
------	---------

Descriptions

Description	GREEN INDICATING LIGHT 12-30VAC/DC LED LGND PLS PO
extra long description	ETN M22-L-G-G-P IP67, IP69K, NEMA 4
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, Complete Indicating Light, Flush, IP67, IP69K, NEMA 4X, 13, Illuminated, Green lens, 100,000 Hours of operation, 12-30 Vac/dc
Product Type	IP67, IP69K, Nema 4X, 13

Manufacturer Information

Brand	Eaton
GTIN	00786685382593
Manufacturers Part Number	M22-L-G-G-P
UPC	786685382593

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Modular pushbutton

Packaging

Carton	1
Weight Per each	0.05



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
and EOEMs

standard

Lloyd's Register Certified, CSA Certified, CCC Marked, Bureau
Veritas, CE Marked, GoST-R