

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



M22DLHRK11RP Red Ext III Mom PB 1NO/1NC 12-30VAC/DC Led LGND PL Eaton Corp

Catalog Number	M22DLHRK11RP
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Complete Device, 22.5 MM, Extended, Momentary, Illuminated, Bezel: Silver, Button: Red,
	1NO-1NC, IP67, IP69K, Nema 4X, 13, 12-30 Vac/DC
Weight per unit	
Product Category	Push Button Complete Assemblie
Features	
actuator	Button, Extended
Contact Configuration	1 NO-1 NC
Voltage Rating	12-30 Vac/dc
Dimensions and Weight	
Depth	1.46
Height	3.45
Size	22.5 mm
Width	1.18
Descriptions	
Description	RED EXT ILL MOM PB 1NO/1NC 12-30VAC/DC LED LGND PL
extra long description	ETN M22-DLH-R-K11-R-P RED EXT ILL M
Features	This attractive, functional line of pushbuttons features a
	space-saving construction that enables fast assembly. The
	complete illuminated M22 line offers LED light units to ensure
	high-quality brightness and up to 100,000 hours of illumination.
	Because of the rugged design of these pushbuttons, most
	operators and contact blocks exceed five million mechanical
	operations.
Long Description	Eaton M22 modular pushbutton, Complete Device, 22.5 mm,
	Extended, Momentary, Illuminated, Bezel: Silver, Button: Red,
Product Type	1NO-1NC, IP67, IP69K, NEMA 4X, 13, 12-30 Vac/dc Red Ext III Mom PB, 1NO/1NC, 12-30VAC/DC
Special Features	M22 series
·	IVIZZ SCI ICS
Manufacturer Information	Fatan
Brand	Eaton
GTIN	00786685382548
Manufacturers Part Number	M22-DLH-R-K11-R-P
Model	Modular pushbutton
UPC	786685382548



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Taxonomies, Classifications, and (Categories
Category Description	MINATURE PILOT DEVICES.22MM
Packaging	
Carton	1
Weight Per each	0.11
Uses, Certifications, and Standard	ds
Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
	and EOEMs
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
standard	CCC Marked,Lloyd's Register Certified,CSA

Certified, GoST-R, Bureau Veritas, CE Marked