



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DRPG Green Mushroom Head PC PB Operator

Eaton Corp

Catalog Number	M22DRPG
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, M22 Modular Mushroom Pushbutton Operator, 22.5 MM, Maintained, Non-Illuminated, Bezel: Silver, Button: Green, IP67, IP69K, Nema 4X, 13, 1, 000, 000 Mechanical Operations
Weight per unit	0.0500 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Mushroom
dimensions	2.5000 IN X 2.5000 IN X 1.5000 IN
operating cycles	1 million

Dimensions and Weight

Depth	2.5000
Height	1.5000
Size	22.5 mm
Width	2.5000

Descriptions

Description	GREEN MUSHROOM HEAD PC PB OPERATOR
extra long description	ETN M22-DRP-G MTN MUSHROOM PB GRN
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, M22 Modular Mushroom Pushbutton Operator, 22.5 mm, Maintained, Non-illuminated, Bezel: Silver, Button: Green, IP67, IP69K, NEMA 4X, 13, 1,000,000 mechanical operations
Product Type	MTN Mushroom PB GRN

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685282725
Manufacturers Part Number	M22-DRP-G
Model	Modular pushbutton
UPC	786685282725



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....MINATURE PILOT DEVICES.22MM

Type.....Modular pushbutton

Packaging

Carton.....1

Weight Per each.....0.05

Uses, Certifications, and Standards

Application.....Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

environmental conditions.....IP67, IP69K

standard.....CCC Marked,Lloyd's Register Certified,CSA

Certified,GoST-R,Bureau Veritas,CE Marked