



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## M22 Modular Pushbutton Operator

**M22S-DH-G**

**UPC:**786685275413

### Dimensions:

- **Height:** .65 IN
- **Length:** 1.17 IN
- **Width:** 1.17 IN

**Weight:**.995 LB

**Notes:**Includes contact block mounting adapter.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Pushbutton
- **Action:** Momentary
- **Actuator:** Extended, Button
- **Bezel:** Black
- **Button Color:** Green
- **Environmental Rating:** IP67, IP69K, NEMA 4x, 13
- **Illumination:** Non-illuminated
- **Operating Cycles:** 5,000,000 Mechanical operations
- **Size:** 22.5 mm
- **Series:** M22

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22\(S\)\(M\)-DH 2D PDF](#)
- [M22\(S\)\(M\)-DH AutoCAD 2D Footprint](#)
- [M22\(S\)\(M\)-DH 2D Drawing Xchange](#)



- [M22\(S\)\(M\)-DH AutoCAD 2D Footprint \(mm\)](#)
- [M22\(S\)\(M\)-DH 3D Model Xchange](#)
- [M22\(S\)\(M\)-DH 3D Inventor](#)
- [M22 Operators and Accessories](#)
- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22S-DH-G](#)
- [Global Data Sheet - M22S-DH-G](#)

**Certifications:**

- CCC Marked
- CSA Certified
- Lloyd's Register Certified

**Product compliance:**

- CE Marked
- Bureau Veritas
- GoST-R



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## M22 Modular Pushbutton Operator

**M22S-DH-G**

**UPC:**786685275413

### Dimensions:

- **Height:** .65 IN
- **Length:** 1.17 IN
- **Width:** 1.17 IN

**Weight:**.995 LB

**Notes:**Includes contact block mounting adapter.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Pushbutton
- **Action:** Momentary
- **Actuator:** Extended, Button
- **Bezel:** Black
- **Button Color:** Green
- **Environmental Rating:** IP67, IP69K, NEMA 4x, 13
- **Illumination:** Non-illuminated
- **Operating Cycles:** 5,000,000 Mechanical operations
- **Size:** 22.5 mm
- **Series:** M22

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22\(S\)\(M\)-DH 2D PDF](#)
- [M22\(S\)\(M\)-DH AutoCAD 2D Footprint](#)
- [M22\(S\)\(M\)-DH 2D Drawing Xchange](#)



- [M22\(S\)\(M\)-DH AutoCAD 2D Footprint \(mm\)](#)
- [M22\(S\)\(M\)-DH 3D Model Xchange](#)
- [M22\(S\)\(M\)-DH 3D Inventor](#)
- [M22 Operators and Accessories](#)
- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22S-DH-G](#)
- [Global Data Sheet - M22S-DH-G](#)

**Certifications:**

- CCC Marked
- CSA Certified
- Lloyd's Register Certified

**Product compliance:**

- CE Marked
- Bureau Veritas
- GoST-R