

Eaton M22-DR-X-SRG

Catalog Number: M22-DR-X-SRG

Eaton 22.5 mm RMQ-Titan Pushbutton, Black, Red, Green Actuator, Silver bezel, IP67, IP69K, Non-illuminated, Flush mounting, NEMA 4X, 13, 1,000,000 operations, Maintained, 22.5 mm, Flush Pushbutton, M22



Photo is representative

General specifications

Product Name

Eaton M22 modular pushbutton

UPC

786685276465

Product Height

1.25 in

Product Weight

0.04 lb

Compliances

CE Marked
Bureau Veritas
GoST-R

Catalog Notes

Includes contact block mounting adapter.
Buttonless operator, comes with three color buttons.

Catalog Number

M22-DR-X-SRG

Product Length/Depth

1.5 in

Product Width

1.75 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CCC Marked
CSA Certified
Lloyd's Register Certified

defaultTaxonomyAttributeLabel

Type

Pushbutton

Actuator color

Black, green, red

Bezel

Silver

Actuator function

Maintained

Enclosure

IP69K

IP67

Button color

Black, red, green

Actuator

Flush, button

Operating mode

Maintained

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Operating cycles

1 million

Mounting method

Flush

Degree of protection

NEMA 13

NEMA 4X

Product category

Flush pushbutton

Size

22.5 mm

Resources

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Drawings

M22(S)(M)-DR AutoCAD 2D Footprint (mm)

M22(S)(M)-DR 2D Drawing Xchange

M22(S)(M)-DR 3D Model Xchange

M22(S)(M)-DR 2D PDF

M22(S)(M)-DR 3D Inventor

M22(S)(M)-DR AutoCAD 2D Footprint

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Eaton Specification Sheet - M22-DR-X-SRG

Global Data Sheet - M22-DR-X-SRG

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)