



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M619427 Self-Laminating Vinyl Wrap Around Labels 1" H X 1"

Brady Worldwide, Inc.

Catalog Number	M619427
Manufacturer	Brady Worldwide, Inc.
Description	Self-Laminating Vinyl Wrap Around Labels 1 In H X 1 In W WT, Clear RL/250
Weight per unit	0.1550 (lbs/each)
Product Category	20230207130857

Features

labels per package	Roll of 250 Labels
Material	Self-Laminating Vinyl
Shape	Square
Temperature Range	-94 °F - 158 °F
Wire Size	0.118 in to 0.199 in

Material, Color, and Finish

Color	White, Clear
Finish	Matte

Dimensions and Weight

Height	1
Size	1 in H x 1 in W
Thickness	0.004
Width	1

Descriptions

Description	SELF-LAMINATING VINYL WRAP AROUND LABELS 1" H X 1"
extra long description	BRADY M6-19-427 Label 1 x 1 Self-la
Features	Self-laminating vinyl material is excellent for wire and cable identification. Designed with a clear protective layer to cover the printed text, B-427 material provides superb protection from abrasion, dirt, oils, solvents, water and excess handling.
Long Description	Self-Laminating Vinyl Wrap Around Labels 1 in H x 1 in W WT, Clear RL/250
Product Type	Label 1 X 1 Self-Lam Vinyl WT/CL RL/250
Special Features	Self Laminating & Wrap Around

Manufacturer Information

Brand	Brady®
GTIN	00888434600368
Manufacturers Part Number	M6-19-427
UPC	888434600368



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Packaging

Carton	1
--------	---

Weight Per each	0.155
-----------------	-------

Uses, Certifications, and Standards

Application	Data and Telecommunications Labeling;Electrical Labeling;Laboratory Labeling;Wire and Cable Labeling
-------------	--

standard	ASTM D 1000;ASTM D 2979;ASTM G 155;UL Recognized
----------	--