ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# MACLLFQWH Maestro 1.5A/75W Fan/LT SP White

*Lutron*

| | |
|---|---|
| Catalog Number | MACLLFQWH |
| Manufacturer | Lutron |
| Description | Maestro Led+ Fan/Light Control, Single-Pole, 120V/75W Dimmable Led or 250W Incandescent/Halogen Light, 1.5A Fan In White, Ed Box Packaging |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Fan Speed Switches & Controls |

## Features

| | |
|---|---|
| actuator | Tapswitch |
| amperage rating | 1.5 A fan |
| connection | Screw Terminal |
| Contact Configuration | N-O |
| Contact Rating | 1.5 A fan |
| media | Yes |
| Voltage Rating | 120 |
| Wattage | 75 W dimmable LED/CFL or 250 W incandescent/halogen light |

## Material, Color, and Finish

| | |
|---|---|
| Color | White |
| Finish | Gloss |

## Dimensions and Weight

| | |
|---|---|
| Size | 4.69 x 2.94 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Descriptions

| | |
|---|---|
| Description | MAESTRO 1.5A/75W FAN/LT SP WHITE |
| extra long description | LUT MACL-LFQ-WH MACL FAN LIGHT WHIT |
| Features | The Lutron Maestro Dual LED+ Dimmer and 4-Speed Fan Control helps you achieve the ideal comfort level for your home. It includes the most advanced technology for superior dimming and adjust the fan speed all from one wall control. The top section is a LED+ Dimmer that works with up to 75W of dimmable LEDs or up to 250W of Incandescent/Halogen bulbs. The bottom section is a 4-speed fan control for a single ceiling paddle fan up to 1.5A. Press the tap switch once to toggle the light or fan ON to a programmed |
| Long Description | Maestro LED+ Fan/Light Control, Single-pole, 120V/75W Dimmable LED or 250W Incandescent/Halogen light, 1.5A fan in White, ED Box packaging |
| Product Type | Macl Fan Light White |
| Special Features | Dimmer (top) Tap on dimmer to preset light level; tap off. Tap twice for full on. Touch rocker to adjust light level. Fan control (bottom) Tap on to preset fan speed; tap off. Touch rocker to adjust speed. 4-quiet fan speeds plus off provide enhanced comfort. Designed to prevent motor hum. For use with only one fan/light. |

## Manufacturer Information

| | |
|---|---|
| Brand | Lutron |
| GTIN | 00784276239523 |
| Manufacturers Part Number | MACL-LFQ-WH |
| UPC | 784276239523 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | CEILING FANS AND ACCESSORIES |
| Type | Digital preset fan/light control |

## Packaging

| | |
|---|---|
| Carton | 24 |
| Package | 48 |
| Weight Per each | 0.3 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Lighting and Fan Control |
| Enclosure | Plastic |
| Mounting | WALLBOX |