

Eaton MB1212L200BTS

Catalog Number: MB1212L200BTS

Eaton residential meter breaker, All-in-ones, 200 A, C, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm#6-350 kcmMain lugs, Surface mounting, 12, Four-jaw, 1, 12, Single-phase, Ringless, Used with BR breakers, 120/240 Vac



General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MB1212L200BTS
UPC	Product Length/Depth
782114849019	5.38 in
Product Height	Product Width
6.75 in	14.44 in
Product Weight	Warranty
28.9 lb	10 year
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

AL : Alabama Power

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

Interrupt rating

10 kAIC

Box size

C

Enclosure

NEMA 3R

Ground

#6-350 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Number of circuits

12

Bus material

Aluminum

Feed type

Top/bottom

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER BREAKER EAST COAST STYLE](#)

Specifications and datasheets

[Eaton Specification Sheet - MB1212L200BTS](#)

[Technical Data Residential Meter Breakers: Type CH and BR Residential](#)

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia