



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Meter Breaker EUSERC

**MBE1212L200BTS**

**UPC:782113493749**

### Dimensions:

- **Height:** 6.3 IN
- **Length:** 26.8 IN
- **Width:** 17.3 IN

**Weight:**39 LB

### Warranties:

- 10 year

### Specifications:

- **Type:** All-in-ones
- **Amperage Rating:** 200A
- **Box Size:** C
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Ground:** #6-2/0 AWG
- **Mounting:** Surface
- **Number Of Circuits:** 12
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Dimensional Drawing - METER BREAKER MBE1212L200BTS, BTF](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Technical Data Residential Meter Breakers: Type CH and BR Residential](#)

### Certifications:



- UL Listed

**Product compliance:**

- EUSERC Approved

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Meter Breaker EUSERC

**MBE1212L200BTS**

**UPC:782113493749**

### Dimensions:

- **Height:** 6.3 IN
- **Length:** 26.8 IN
- **Width:** 17.3 IN

**Weight:**39 LB

### Warranties:

- 10 year

### Specifications:

- **Type:** All-in-ones
- **Amperage Rating:** 200A
- **Box Size:** C
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Ground:** #6-2/0 AWG
- **Mounting:** Surface
- **Number Of Circuits:** 12
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Dimensional Drawing - METER BREAKER MBE1212L200BTS, BTF](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Technical Data Residential Meter Breakers: Type CH and BR Residential](#)

### Certifications:



- UL Listed

**Product compliance:**

- EUSERC Approved

---

© 2016 Eaton. All rights reserved.