

# Eaton MBE48B200BTS

Catalog Number: MBE48B200BTS

Eaton Meter Breaker EUSERC Type BR , CSR2200 main breaker, 200 A, 120/240V, Ring, 4 spaces, 8 circuits, 10 kAIC, Surface mounting, Box size A, Aluminum bus, Overhead/underground feed, Four-jaws, #6-250 kcmil line, #6-250 kcmil ground

## General specifications

Product Name	Catalog Number
Eaton meter breaker EUSERC	MBE48B200BTS
UPC	Product Length/Depth
782114849217	5.38 in
Product Height	Product Width
6.9 in	14.44 in
Product Weight	Warranty
28 lb	10 year
Compliances	Certifications
EUSERC Approved	UL Listed



## Product specifications

### Interrupt rating

10 kAIC

### Utility approvals

AZ : Arizona Public Service Company

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

NM : El Paso Electric

TX : El Paso Electric

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

AZ : Salt River Project (SRP)

CA : PacifiCorp/Pacific Power/Rocky Mountain Power

ID : PacifiCorp/Pacific Power/Rocky Mountain Power

OR : PacifiCorp/Pacific Power/Rocky Mountain Power

UT : PacifiCorp/Pacific Power/Rocky Mountain Power

WA : PacifiCorp/Pacific Power/Rocky Mountain Power

WY : PacifiCorp/Pacific Power/Rocky Mountain Power

HI : Hawaiian Electric

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

WA : Puget Sound Energy

WA : Tacoma Public Utilities

NC : Dominion

VA : Dominion

### Phase

Single-phase

### Ground

#6-250 kcmil

### Bus material

Aluminum

### Number of jaws

Four-jaw

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER BREAKER WEST COAST STYLE

### Specifications and datasheets

Technical Data Residential Meter Breakers: Type CH and BR Residential

Eaton Specification Sheet - MBE48B200BTS

Main circuit breaker

CSR2200

Enclosure

NEMA 3R

Type

All-in-ones

Feed type

Top/bottom

Number of sockets

1

Used with

Type BR breakers

Voltage rating

120/240 V

Number of circuits

8

Box size

A



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)