



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MC128WG500 12/8 Homerun 2BK, 2RD, 2BL, 2WH, 1 GRN GRD *Southwire Company*

|                  |                                       |
|------------------|---------------------------------------|
| Catalog Number   | MC128WG500                            |
| Manufacturer     | Southwire Company                     |
| Description      | 12-4/12-4/12-1MC-Plus 2BK 2RD 4WE 1GN |
| Weight per unit  | 0.2620 (lbs/each)                     |
| Product Category | Steel Armor Copper Conductors         |

### Features

|                      |    |
|----------------------|----|
| Conductor Size       | 12 |
| Number of Conductors | 8  |

### Material, Color, and Finish

|                    |              |
|--------------------|--------------|
| Conductor Material | Solid Copper |
|--------------------|--------------|

### Descriptions

|                        |                                            |
|------------------------|--------------------------------------------|
| Description            | 12/8 HOMERUN 2BK, 2RD, 2BL, 2WH, 1 GRN GRD |
| extra long description | KT 3906-42-00 12-4/12-4/12-1 MCPLUS        |
| Long Description       | 12-4/12-4/12-1MC-PLUS 2BK 2RD 4WE 1GN      |
| Product Type           | 12-4/12-4/12-1 MCPLUS2BK 2RD 4WE 1GN       |

### Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Flexible Conduit |
| GTIN                      | 00077680259516   |
| Manufacturers Part Number | 3906-42-00       |
| UPC                       | 077680259516     |

### Taxonomies, Classifications, and Categories

|                      |                                                |
|----------------------|------------------------------------------------|
| Category Description | BUILDING WIRE                                  |
| Type                 | MC-Plus® Neutral Per Phase Steel Armored Cable |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 500   |
| Weight Per each | 0.262 |

### Uses, Certifications, and Standards

|          |                                                                                                                                                                                                                                                                                             |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| standard | UL 83, 1479, 1569, 1581, 2556, File Reference E80042 NEC® 210.4(B), 230.43, 300.22(C), 330, 392, 396.10(A), 645Federal Specification A-A-59544 (formerly J-C-30B) Meets all applicable OSHA and HUD Requirements UL Classified 1, 2, and 3 hour through (Fire) penetration product, R-14141 |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|