



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725



MCP39PAR30LNU830 39W PAR30 MH Med Base Clear High Cri Open Ceram Ar *Sylvania-Ledvance*

Catalog Number	MCP39PAR30LNU830
Manufacturer	Sylvania-Ledvance
Description	Metal Halide Lamp, Metal Halide; 39 W; Shape Designation PAR30LN; E26 Medium Base; Ansi Code/Ballast C130/O, Pulse Start; Initial Intensity 2300 Lumen; Color Rendering Index 85; Color Temperature 3000 K; Operating Position Universal
Weight per unit	1.0 (lbs/each)
Product Category	Hid Ceramic Metal Halide Lamps

Features

ANSI Code/Ballast	C130/O, PULSE START
Distribution/Beam Spread	30 DEG
Initial Intensity	2300 LUMEN
Operating Position	Universal
Overall Length in inch	4.76 IN
Wattage	39 W

Material, Color, and Finish

Base Type	E26 Medium
Color Rendering Index	85 mm
Color Temperature in Kelvin	3000 K

Dimensions and Weight

Overall Length	4.76 INCH
----------------	-----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725

Descriptions

Commodity Description	MERCURY VAPOR & QUARTZ LAMPS
Description	39W PAR30 MH MED BASE CLEAR HIGH CRI OPEN CERAM AR
extra long description	METAL HALIDE TYPE; 4.76 INCH OVERALL LENGTH; 4.76 OVERALL LENGTH IN INCH; OPEN/ENCLOSED FIXTURE APPLICATION; 6 STANDARD PACKAGE; 39 W WATTAGE; E26 MEDIUM BASE TYPE; 12000 LIFE IN HOUR; PAR30LN SHAPE DESIGNATION; 3000; 85 COLOR RENDERING INDEX; 30 DEG DISTRIBUTION/BEAM SPREAD; 2300 LUMEN INITIAL INTENSITY; UNIVERSAL OPERATING POSITION; C130/O, PULSE START ANSI CODE/BALLAST; ECOLOGIC[R] BRAND
Long Description	METAL HALIDE LAMP, METAL HALIDE; 39 W; SHAPE DESIGNATION PAR30LN; E26 MEDIUM BASE; ANSI CODE/BALLAST C130/O, PULSE START; INITIAL INTENSITY 2300 LUMEN; COLOR RENDERING INDEX 85; COLOR TEMPERATURE 3000 K; OPERATING POSITION UNIVERSAL
Product Type	Metal Halide Lamp

Manufacturer Information

Brand	OSRAM SYLVANIA
GTIN	00046135648816
Manufacturers Part Number	MCP39PAR30LN/U/830/FL/ECO-PB
UPC	046135648816

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
Type	METAL HALIDE

Packaging

Carton	1
Package	6
Standard Package	6 in
Weight Per each	1

Uses, Certifications, and Standards

Application	OPEN/ENCLOSED FIXTURE
-------------	-----------------------