



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MD2 1/4 X 4" Masonry Drill Bit (Carbide Tip)

*L.H. Dottie CO.*

Catalog Number	MD2
Manufacturer	L.H. Dottie CO.
Description	Masonry Drill Bit, 1/4 In Bit Size, 1/4 In Shank Diameter, Tungsten Carbide Material, Black Oxide, 4 In Overall Length, 0.04 LB
Weight per unit	0.0400 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Drill Size	1/4 in
Shank Size	1/4 IN
Shank Type	STRAIGHT

### Material, Color, and Finish

Finish	BLACK OXIDE
--------	-------------

### Descriptions

Description	1/4 X 4" MASONRY DRILL BIT (CARBIDE TIP)
Special Features	Tempered body for long life ; Slow spiral ; Suitable for rotary or percussion

### Manufacturer Information

Brand	Dottie
GTIN	00781002302100
UPC	781002302100

### Taxonomies, Classifications, and Categories

Category Description	ANCHORS & ANCHOR KITS
Type	Masonry Drill

### Packaging

Carton	1
Weight Per each	0.04

### Uses, Certifications, and Standards

Application	For Brick, Concrete, Tile, Slate And Cinder Block
-------------	---



**L.H. Dottie Company**  
 6131 Garfield Avenue  
 Commerce, California 90040  
 Call: 323-725-1000 • Fax: 323-721-0000

**"Building a Better Brand"**

## Item # MD2, (MD2) Carbide Tip Masonry Drill Bit

1/4 x 4" Masonry Drill Bit (Carbide Tip)



### Product Specifications | Packaging Specifications

#### Product Specifications

<b>Category Number</b>	6320
<b>UPC Code</b>	781002302100
<b>Price per Quantity</b>	1
<b>Sort</b>	2724
<b>Size</b>	1/4 x 4 in.
<b>Diameter</b>	1/4 in.
<b>Length</b>	4 in.
<b>Shank Length</b>	1/4 in.

#### Packaging Specifications

<b>Unit Quantity</b>	1
----------------------	---

<b>Carton Quantity</b>	10
<b>Unit (UM)</b>	Each
<b>Package Length</b>	5.43 in.
<b>Package Width</b>	1.50 in.
<b>Package Height</b>	0.16 in.
<b>Package Weight</b>	0.0005 lb.
<b>United Nations Standard Products &amp; Services Code (UNSPSC)</b>	27111543