




## NON-METALLIC LOW PROFILE WIU COVERS

Single Gang Flat Expandable While-In-Use Covers - Extra Duty<sup>®</sup>  
Horizontal/Vertical 16-in-1

C07.1



Catalog #: ML500G

## APPLICATIONS

Low profile design that is expandable for weatherproof protection while an outlet is in use.

## PRODUCT FEATURES

Revolutionary patented design expands from 1" to 3" for while-in-use needs  
100% paintable surface  
Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight  
Patented Quick-Fit<sup>™</sup> keyhole mounting system allows installation in under a minute.  
Includes attached gasket and mounting hardware

## UL LISTED

File E116141

## NEMA

3R Rated

## NEC

2014 Compliant (article 406.9A &amp; B) Extra Duty Rated

## US PATENTS

8,101,861; 8,319,334; 8,053,671

## GENERAL PRODUCT INFORMATION

Color: Gray

## CONFIGURATION

Gangs: 1

## PRODUCT MEASUREMENTS

Depth: 1 in. to 3 in.  
Wt. Ea. (Lbs.): 0.410

## PACKAGING


Package Type: Shrink  
Std. Pkg.: 10  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 41.00  
Ship Carton Length (in.): 13.13  
Ship Carton Width (in.): 4.38  
Ship Carton Height (in.): 6.63  
Ctn Weight (Lbs.): 4.10  
Pallet Qty: 1800.00  
UPC Number: 050169917411  
I2of5: 50050169917416



**NON-METALLIC LOW PROFILE WIU COVERS**

**Single Gang Flat Expandable While-In-Use Covers - Extra Duty<sup>®</sup>**  
**Horizontal/Vertical 16-in-1**

**C07.1**



Catalog #: ML500G

**APPLICATIONS**

Low profile design that is expandable for weatherproof protection while an outlet is in use.

**PRODUCT FEATURES**

Revolutionary patented design expands from 1" to 3" for while-in-use needs  
100% paintable surface  
Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight  
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.  
Includes attached gasket and mounting hardware

**UL LISTED**

File E116141

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A & B) Extra Duty Rated

**US PATENTS**

8,101,861; 8,319,334; 8,053,671

**GENERAL PRODUCT INFORMATION**

Color: Gray

**CONFIGURATION**

Gangs: 1

**PRODUCT MEASUREMENTS**

Depth: 1 in. to 3 in.  
Wt. Ea. (Lbs.): 0.410

**PACKAGING**

Package Type: Shrink  
Std. Pkg.: 10  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 41.00  
Ship Carton Length (in.): 13.13  
Ship Carton Width (in.): 4.38  
Ship Carton Height (in.): 6.63  
Ctn Weight (Lbs.): 4.10  
Pallet Qty: 1800.00  
UPC Number: 050169917411  
I2of5: 50050169917416