



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



N250SP 250 Al/Cu Split Bolt

Nsi Industries

| | |
|------------------|---|
| Catalog Number | N250SP |
| Manufacturer | Nsi Industries |
| Description | All Purpose Split Bolt Connector 250 MCM All Purpose Split Bolt Connectors Are Used For Combinations Of Aluminum to Copper, Aluminum to Aluminum, Steel to Aluminum, Copper to Copper, and Steel to Copper Applications. They Have An Electro-Tinned Body. UI Listed For Copper and Copperweld Wires Only. Includes Nut, Spacer and Pressure Pad. |
| Weight per unit | 0.5700 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|-------------------|
| Material | TIN PLATED COPPER |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 1/0 STR - 250 MCM |
| Wire Type | Class A & B |

Material, Color, and Finish

| | |
|--------|-------------------|
| Color | Tin Plated Copper |
| Finish | Tin Plated Copper |

Dimensions and Weight

| | |
|------|-------------------|
| Size | L=2.106 - W=1.102 |
|------|-------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 250 AL/CU SPLIT BOLT |
| extra long description | NSI N-250SP Copper Split Bolt 2/0 T |
| Features | All Purpose Split Bolt Connector 250 MCM All Purpose Split Bolt Connectors are used for combinations of aluminum to copper, aluminum to aluminum, steel to aluminum, copper to copper, and steel to copper applications. They have an electro-tinned body. UL listed for copper and copperweld wires only. Includes nut, spacer and pressure pad. |
| Long Description | All Purpose Split Bolt Connector 250 MCM All Purpose Split Bolt Connectors are used for combinations of aluminum to copper, aluminum to aluminum, steel to aluminum, copper to copper, and steel to copper applications. They have an electro-tinned body. UL listed for copper and copperweld wires only. Includes nut, spacer and pressure pad. |
| Product Type | Copper Split Bolt 2/0 Tin Plated |
| Special Features | 1/0 SOL-250 MCM - 6 Pack |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381020390 |
| Manufacturers Part Number | N-250SP |
| UPC | 662381020390 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------|
| Category Description | SPLIT BOLTS |
| Type | Tin Plated Copper Split Bolt |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.57 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL486B |
| Temperature Rating | 90 C |