



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P1E18MC250AT 250A 277/480 3P4W AL

Siemens Industry Inc

Catalog Number	P1E18MC250AT
Manufacturer	Siemens Industry Inc
Description	Circuit Breaker Panelboard, 20 Inch Width X 5.75 Inch Depth X 32 Inch Height Size; Aluminum Enclosure Material; UL 67 Approval; 480 Star/277 Volt Voltage Rating; Surface Mounting; Type 1/3R/12 Enclosure; 250 Amp Current Rating; 18 Circuit(S)
Weight per unit	N/A
Product Category	Lighting Panelboard Boxes

Features

Current Rating	250 Amp
Number of Circuits	18
Voltage Rating	480 Star/277 Volt

Material, Color, and Finish

Enclosure Material	ALUMINUM
--------------------	----------

Dimensions and Weight

Size	20 Inch Width x 5.75 Inch Depth x 32 Inch Height
------	--

Descriptions

Commodity Description	LIGHTING PANELBOARD BOXES
Description	250A 277/480 3P4W AL
extra long description	20 INCH WIDTH X 5.75 INCH DEPTH X 32 INCH HEIGHT SIZE; ALUMINUM ENCLOSURE MATERIAL; UL 67 APPROVAL; 480 STAR/277 VOLT VOLTAGE RATING; SURFACE MOUNTING; TYPE 1/3R/12 ENCLOSURE; 250 AMP CURRENT RATING; 18 CIRCUIT(S); 3-PHASE 4-WIRE MAIN CIRCUIT CONFIGURATION
Long Description	CIRCUIT BREAKER PANELBOARD, 20 INCH WIDTH X 5.75 INCH DEPTH X 32 INCH HEIGHT SIZE; ALUMINUM ENCLOSURE MATERIAL; UL 67 APPROVAL; 480 STAR/277 VOLT VOLTAGE RATING; SURFACE MOUNTING; TYPE 1/3R/12 ENCLOSURE; 250 AMP CURRENT RATING; 18 CIRCUIT(S)
Product Type	Circuit Breaker Panelboard

Manufacturer Information

Brand	SIEMENS MOTORS/CONTROLS/CIRCUIT BREAKERS
GTIN	00887621663513
Manufacturers Part Number	P1E18MC250AT
UPC	887621663513



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL 67
Enclosure	Type 1/3R/12
Mounting	SURFACE