



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P4010ACSC0W CO/Smoke Detector *Kidde Safety*

Catalog Number	P4010ACSC0W
Manufacturer	Kidde Safety
Description	Combination Smoke and Carbon Monoxide Alarm, Smoke and Carbon Monoxide Alarm, Battery Powered Type; Photoelectric/Electrochemical Operation Type; UL 217/2034, Nfpa 72 Approval; 85 Decibel At 10 Foot Horn Type; 120 Volt Ac 60 Hertz Voltage Rating/Source
Weight per unit	0.6000 (lbs/each)
Product Category	Smoke & Heat Detectors

Features

Horn Type	85 Decibel at 10 Foot
LED/Strobe Type	Flashing LED
Number of Interconnections	24 in
Operation Type	Photoelectric/Electrochemical
Voltage Rating/Source	120 Volt AC 60 Hertz

Descriptions

Additional Information	Overall Dimension 5.59 Inch Diameter x 1.91 Inch Depth; Battery Type 3 Volt Sealed-In Lithium; Relative Humidity Rating 10 to 95 Percent RH (Non-Condensing); Temperature Rating 40 to 100 Deg F
Commodity Description	SMOKE & HEAT DETECTORS
Description	CO/SMOKE DETECTOR
Long Description	COMBINATION SMOKE AND CARBON MONOXIDE ALARM, SMOKE AND CARBON MONOXIDE ALARM, BATTERY POWERED TYPE; PHOTOELECTRIC/ELECTROCHEMICAL OPERATION TYPE; UL 217/2034, NFPA 72 APPROVAL; 85 DECIBEL AT 10 FOOT HORN TYPE; 120 VOLT AC 60 HERTZ VOLTAGE RATING/SOURCE
Product Type	Combination Smoke and Carbon Monoxide Alarm

Manufacturer Information

Brand	Kidde
GTIN	00047871273232
Manufacturers Part Number	21027323
UPC	047871273232

Taxonomies, Classifications, and Categories

Type	Smoke and Carbon Monoxide Alarm, Battery Powered
------	--

Packaging

Carton	1
Weight Per each	0.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Approval

UL 217/2034, NFPA 72