



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PAR112 1-1/2" Parallel CLMP

Robroy/Ecn Korns

Catalog Number	PAR112
Manufacturer	Robroy/Ecn Korns
Description	Conduit Support, Parallel; Electro Plated; Malleable Iron; Trade Size 1-1/2 Inch; Standard Package 25 Per Carton
Weight per unit	0.9300 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

Material	MALLEABLE IRON
Trade Size	1-1/2 INCH

Material, Color, and Finish

Finish	HOT DIP GALVANIZED
--------	--------------------

Descriptions

Additional Information	Applicable standard ANSI C80.1
Also Known As...	PC Clamp Parallel Clamp (PC)
Commodity Description	Rigid Conduit Fittings - Steel
Long Description	CONDUIT SUPPORT, PARALLEL; ELECTRO PLATED; MALLEABLE IRON; TRADE SIZE 1-1/2 INCH; STANDARD PACKAGE 25 PER CARTON
Product Type	Conduit Support

Manufacturer Information

Brand	ECN-KORNS
GTIN	00784011154166
Manufacturers Part Number	KNPAR-1-1/2
Model	KNPAR
UPC	784011154166

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	PARALLEL

Packaging

Carton	1
Package	25
Standard Package	25 PER CARTON
Weight Per each	0.93

Uses, Certifications, and Standards


Approval	UL 6, CSA C22.2
----------	-----------------

HOT DIP GALVANIZED CLAMPS AND CONDUIT SUPPORT

THE ORIGINAL KORN'S CLAMP

Malleable iron—

Hot dip galvanized—standard. Also available with various grades of stainless steel hardware. Contact Korn's representative or factory for pricing.



RIGHT ANGLE CONDUIT SUPPORTS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON
KNRA-3/8	3/8 RIGHT ANGLE CLAMP	25	50
KNRA-1/2	1/2 RIGHT ANGLE CLAMP	40	50
KNRA-3/4	3/4 RIGHT ANGLE CLAMP	43	50
KNRA-1	1 RIGHT ANGLE CLAMP	48	25
KNRA-1-1/4	1 1/4 RIGHT ANGLE CLAMP	53	25
KNRA-1-1/2	1 1/2 RIGHT ANGLE CLAMP	58	25
KNRA-2	2 RIGHT ANGLE CLAMP	85	25
KNRA-2-1/2	2 1/2 RIGHT ANGLE CLAMP	106	20
KNRA-3	3 RIGHT ANGLE CLAMP	110	15
KNRA-3-1/2	3 1/2 RIGHT ANGLE CLAMP	128	15
KNRA-4	4 RIGHT ANGLE CLAMP	140	10
KNRA-5	5 RIGHT ANGLE CLAMP	330	5
KNRA-6	6 RIGHT ANGLE CLAMP	375	5



PARALLEL CONDUIT SUPPORTS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON
KNPAR-3/8	3/8 PARALLEL CLAMP	32	50
KNPAR-1/2	1/2 PARALLEL CLAMP	58	40
KNPAR-3/4	3/4 PARALLEL CLAMP	64	30
KNPAR-1	1 PARALLEL CLAMP	70	30
KNPAR-1-1/4	1 1/4 PARALLEL CLAMP	72	25
KNPAR-1-1/2	1 1/2 PARALLEL CLAMP	93	20
KNPAR-2	2 PARALLEL CLAMP	100	20
KNPAR-2-1/2	2 1/2 PARALLEL CLAMP	135	15
KNPAR-3	3 PARALLEL CLAMP	155	10
KNPAR-3-1/2	3 1/2 PARALLEL CLAMP	190	10
KNPAR-4	4 PARALLEL CLAMP	205	10



EDGE TYPE CONDUIT SUPPORTS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON
KNET-1/2	1/2 EDGE CLAMP	67	30
KNET-3/4	3/4 EDGE CLAMP	71	30
KNET-1	1 EDGE CLAMP	85	20
KNET-1-1/4	1 1/4 EDGE CLAMP	91	20
KNET-1-1/2	1 1/2 EDGE CLAMP	115	20
KNET-2	2 EDGE CLAMP	135	15
KNET-2-1/2	2 1/2 EDGE CLAMP	183	10
KNET-3	3 EDGE CLAMP	230	5