

Support Products

Pipe Straps

Plasti-Bond PVC coated pipe straps are used to securely mount conduit to a wall or other structure for support. They are available in two styles: a one-hole malleable iron strap or a two-hole stamped steel strap. Mounting hardware not provided.

Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



**CONDUIT PIPE STRAP
1 HOLE**

PIPE SIZE	FERROUS CATALOG #	NOMINAL WT. FOR 100
1/2"	PBPS11M	11
3/4"	PBPS22M	14
1"	PBPS33M	12
1-1/4"	PBPS44M	25
1-1/2"	PBPS55M	36
2"	PBPS66M	71
2-1/2"	PBPS77M	111
3"	PBPS88M	134
3-1/2"	PBPS99M	166
4"	PBPS100M	256



**CONDUIT PIPE STRAP
2 HOLE**

PIPE SIZE	FERROUS CATALOG #	NOMINAL WT. FOR 100
1/2"	PBPS11S-2	2.0
3/4"	PBPS22S-2	3.0
1"	PBPS33S-2	4.0
1-1/4"	PBPS44S-2	4.5
1-1/2"	PBPS55S-2	5.0
2"	PBPS66S-2	10.0
2-1/2"	PBPS77S-2	13.0
3"	PBPS88S-2	17.0
3-1/2"	PBPS99S-2	20.0
4"	PBPS100S-2	25.0

Clamp Back Spacers

Plasti-Bond PVC coated clamp back spacers are used with malleable or stamped pipe straps to provide a mounting stand-off for a conduit from a wall or other structure.

Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



CONDUIT CLAMP BACK SPACER

PIPE SIZE	FERROUS CATALOG #	NOMINAL WT. EACH
1/2"	PBCLB-M50	0.1
3/4"	PBCLB-M75	0.1
1"	PBCLB-M100	0.1
1-1/4"	PBCLB-M125	0.2
1-1/2"	PBCLB-M150	0.2
2"	PBCLB-M200	0.3
2-1/2"	PBCLB-M250	1.0
3"	PBCLB-M300	1.7
4"	PBCLB-M400	2.0

Conduit Clamp Hangers

Plasti-Bond PVC coated conduit clamp hangers are used with threaded rod to securely suspend conduit runs supported from above. They are provided with stainless steel hardware.

Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



CONDUIT HANGER

PIPE SIZE	CATALOG #	NOMINAL WEIGHT
1/2"	PB6H0B	0.1
3/4"	PB6H1B	0.1
1"	PB6H2B	0.1
1-1/4"	PB6H3B	0.1
1-1/2"	PB6H4B	0.2
2"	PB6H5B	0.3
2-1/2"	PB6H6B	0.4
3"	PB6H7B	0.5
3-1/2"	PB6H8B	0.6
4"	PB6H9B	0.7

Thread Rods

Plasti-Bond PVC coated all thread rod is used with coated conduit hangers and coated strut to securely suspend conduit runs supported from above. It is provided in 3/8" and 1/2" sizes and three standard lengths, 3', 6' and 10'.

Features:

- 20 mil gray PVC exterior coating
- 2 trade sizes and 3 standard lengths



THREAD RODS

SIZE	CATALOG #
3/8" X 3'	PBH193-3/8X3
3/8" X 6'	PBH193-3/8X6
3/8" X 10'	PBH193-3/8X10
1/2" X 3'	PBH193-1/2X3
1/2" X 6'	PBH193-1/2X6
1/2" X 10'	PBH193-1/2X10



Contact us:
customerservice@plastibond.com



Visit www.plastibond.com
For more information

Support Products

Pipe Straps

Plasti-Bond PVC coated pipe straps are used to securely mount conduit to a wall or other structure for support. They are available in two styles: a one-hole malleable iron strap or a two-hole stamped steel strap. Mounting hardware not provided.

Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



CONDUIT PIPE STRAP 1 HOLE

PIPE SIZE	FERROUS CATALOG #	NOMINAL WT. FOR 100
1/2"	PBPS11M	11
3/4"	PBPS22M	14
1"	PBPS33M	12
1-1/4"	PBPS44M	25
1-1/2"	PBPS55M	36
2"	PBPS66M	71
2-1/2"	PBPS77M	111
3"	PBPS88M	134
3-1/2"	PBPS99M	166
4"	PBPS100M	256

CONDUIT PIPE STRAP 2 HOLE

PIPE SIZE	FERROUS CATALOG #	NOMINAL WT. FOR 100
1/2"	PBPS11S-2	2.0
3/4"	PBPS22S-2	3.0
1"	PBPS33S-2	4.0
1-1/4"	PBPS44S-2	4.5
1-1/2"	PBPS55S-2	5.0
2"	PBPS66S-2	10.0
2-1/2"	PBPS77S-2	13.0
3"	PBPS88S-2	17.0
3-1/2"	PBPS99S-2	20.0
4"	PBPS100S-2	25.0

Clamp Back Spacers

Plasti-Bond PVC coated clamp back spacers are used with malleable or stamped pipe straps to provide a mounting stand-off for a conduit from a wall or other structure.

Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



CONDUIT CLAMP BACK SPACER

PIPE SIZE	FERROUS CATALOG #	NOMINAL WT. EACH
1/2"	PBCLB-M50	0.1
3/4"	PBCLB-M75	0.1
1"	PBCLB-M100	0.1
1-1/4"	PBCLB-M125	0.2
1-1/2"	PBCLB-M150	0.2
2"	PBCLB-M200	0.3
2-1/2"	PBCLB-M250	1.0
3"	PBCLB-M300	1.7
4"	PBCLB-M400	2.0

Conduit Clamp Hangers

Plasti-Bond PVC coated conduit clamp hangers are used with threaded rod to securely suspend conduit runs supported from above. They are provided with stainless steel hardware.

Features:

- 20 mil gray PVC exterior coating
- 10 trade sizes from 1/2" through 4"



CONDUIT HANGER

PIPE SIZE	CATALOG #	NOMINAL WEIGHT
1/2"	PB6H0B	0.1
3/4"	PB6H1B	0.1
1"	PB6H2B	0.1
1-1/4"	PB6H3B	0.1
1-1/2"	PB6H4B	0.2
2"	PB6H5B	0.3
2-1/2"	PB6H6B	0.4
3"	PB6H7B	0.5
3-1/2"	PB6H8B	0.6
4"	PB6H9B	0.7

Thread Rods

Plasti-Bond PVC coated all thread rod is used with coated conduit hangers and coated strut to securely suspend conduit runs supported from above. It is provided in 3/8" and 1/2" sizes and three standard lengths, 3', 6' and 10'.

Features:

- 20 mil gray PVC exterior coating
- 2 trade sizes and 3 standard lengths



THREAD RODS

SIZE	CATALOG #
3/8" X 3'	PBH193-3/8X3
3/8" X 6'	PBH193-3/8X6
3/8" X 10'	PBH193-3/8X10
1/2" X 3'	PBH193-1/2X3
1/2" X 6'	PBH193-1/2X6
1/2" X 10'	PBH193-1/2X10



Contact us:
customerservice@plastibond.com



Visit www.plastibond.com
For more information