



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PD5NEWH Caseta 500W Elv Mult W/Neutral White Lutron

| | |
|------------------|--|
| Catalog Number | PD5NEWH |
| Manufacturer | Lutron |
| Description | Lutron Caseta Wireless Elv+ Smart Dimmer Switch, With Phase Selectable Dimming For Led (250W), MLV (400W), Elv (500W), and Incandescent/Halogen (500W) Lighting, 120V, White |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|-------------|
| Connection Type | Wire Leads |
| insulation | Plastic |
| media | Yes |
| Poles | 1 |
| Switch Type | Push button |
| Voltage Rating | 120 |
| Wattage | 500 |

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.69 x 2.94;119 x 75 |
|------|----------------------|

Descriptions

| | |
|------------------------|--|
| Description | CASETA 500W ELV MULT W/NEUTRAL WHITE |
| extra long description | LUT PD-5NE-WH Caseta ELV Dimmer 250 |
| Features | The Caseta ELV+ Smart Dimmer Switch with phase selectable dimming works with up to 250W of dimmable LED, 500W of incandescent/halogen/electronic low-voltage (ELV), or 400-Watt of magnetic low-voltage (MLV); Neutral wire connection and 10-Watt minimum load required for all load types. Out of the box, the dimmer is set to reverse phase for ELV/incandescent/halogen light loads. However, since it is phase selective, the dimmer output can be changed to forward phase for MLV lighting loads and other certain LED |
| Long Description | Lutron Caseta Wireless ELV+ Smart Dimmer Switch, with Phase Selectable Dimming for LED (250W), MLV (400W), ELV (500W), and Incandescent/Halogen (500W) lighting, 120V, White |
| Product Type | Caséta Elv Dimmer 250W Led White |
| Special Features | Controls 250 W LED (screw-base), 500 W incandescent/halogen, 400 VA (300 W) magnetic low-voltage, 500 W electronic low-voltage, 400 W Hi-lume 1 percent 2-wire LED driver, or 3.3 A Tu-Wire fluorescent ballast loads. Simple, intuitive design with on, off and raise/lower buttons. Provides true dimming from each location with Pico wireless remotes. |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Lutron |
| GTIN | 00784276217699 |
| Manufacturers Part Number | PD-5NE-WH |
| UPC | 784276217699 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Wireless in-wall dimmer, multi-location/single-pole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.25 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | 0 to 90% humidity, non-condensing. Indoor use only. |
| Mounting | WALLBOX |
| standard | UL, CUL, FCC, NOM, ICC, IFTEL |